

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130105-0045](#)
Status: **Active**
Overview: Specialty Lighting
Description: Haztex® Incandescent Hazardous and Wet Location Hand Lamp with LOVOLT® In-line Transformer 100W, 16/3 SOOW Primary Cord Type, Cord Length 7.62m (25.0')

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification

CSA	LR39801
UL	E30252

General

Product Family	Portable Lighting
Series	130105
Comments	Class I, Division I, Groups C and D (flammable gases and vapors); Class II, Division I, Groups F and G (ignitable dust); Class I, Zone I, Group IIB (UL)
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Outlet	None
Overview	Specialty Lighting
Product Literature Order No	987650-8052
Product Name	Haztex®
Type	Specialty Light
UPC	78678862505
Woodhead	Yes

Physical

Cord Length - Primary	3.04m (10.0')
Cord Length - Secondary	7.62m (25.0')
Depth	127.00mm (5.000")
Duty	Hazardous, Wet Location
Guard Included	No
Guard Type	N/A
Height	419.10mm (16.500")
Length	N/A
Material - Globe	Tempered Soda-Lime Glass
Material - Guard	Cast Aluminum
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A

Electrical

Bulb Type	Incandescent
Cord Type - Primary	16/3 SOOW
Cord Type - Secondary	14/3 SOOW
Lamp Type	A21
Lamp Wattage - Maximum	75W
Lumens	750
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Voltage (Secondary) - Maximum	12V AC

Material Info

Old Part Number	1635-12A
-----------------	----------



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[130105Series](#)

This document was generated on 12/10/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION