

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [120086-0148](#)  
**Status:** **Active**  
**Overview:** [Brad® Nano-Change® &#40;M8&#41; Products](#)  
**Description:** Nano-Change® (M8) Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 24 AWG, PVC Cable, 6.0m (19.68') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120086](#)  
 Connector End A Nano-Change® (M8)  
 Connector End B Pigtail  
 IP Rating IP68  
 Overview [Brad® Nano-Change® &#40;M8&#41; Products](#)  
 Product Name Nano-Change® (M8)  
 Protocol N/A  
 Region America  
 Type Single Ended  
 UPC 78678838667

**Physical**

Cable Diameter 4.57mm (.180")  
 Cable Length 6.0m (19.68')  
 Color - Cable Jacket Yellow  
 Coupling Style Threaded  
 Gender Female-Pigtail  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body TPE  
 Material - Contact Copper Alloy  
 Material - Coupling Nut Nickel-plated Brass  
 Material - O-Ring Viton  
 Material - Plating Mating Gold  
 Orientation Straight  
 Poles 4  
 Temperature Range - Operating -20°C to +105°C  
 Wire Size AWG 24  
 Wire/Cable Type UL 2661

**Electrical**

Current - Maximum per Contact 3A  
 Voltage - Maximum 60V AC / 75V DC

**Material Info**

Old Part Number 404000A10M060

**Reference - Drawing Numbers**

Sales Drawing SD-120086-102



**EU RoHS**

**ELV and RoHS  
 Compliant**  
**REACH SVHC  
 Not Reviewed**  
**Low-Halogen Status  
 Not Reviewed**

**China RoHS**



**Need more information on product  
 environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of  
 Compliance, [click here](#)

Please visit the [Contact Us](#) section for any  
 non-product compliance questions.

**Search Parts in this Series**

120086Series

This document was generated on 10/02/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**