



# MARKETING SALES DRAWING



**DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING**  
**DIMENSIONS IN METRIC [ ]**

This drawing is the property of  
 Tusonix, Inc., and may not be  
 used, reproduced, published or  
 disclosed to others without ex-  
 pressed authorization by Tusonix Inc.

Electrical Testing  
 per Tusonix standard  
 test plans and Mil-Std-202  
 Test Methods.



ORIENTATION



NOTES:

1. OPERATING TEMP. RANGE: -55°C TO +125°C.
2. SILVER PLATED CASE, LEAD, AND MOUNTING HARDWARE.
3. MAX. RECOMMENDED MOUNTING TORQUE : 2.0 in. lb. [0.23 Nm]
4. MAX. RECOMMENDED SOLDERING TEMPERATURE : 260° C.  
SEE INSTALLATION RECOMMENDATIONS.
5. LOCK WASHER INCLUDED.
6. TUSONIX STANDARD PART NUMBER: 4400-682.  
TUSONIX RoHS COMPLIANT PART NUMBER: 4400-682 LF.  
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART  
NUMBER WHEN ORDERING.
7. PART MARKING: TRADEMARK AND VARIATION NUMBER ON  
HEX FLATS. STANDARD PART: BLACK INK. RoHS PART:  
DARK GREEN INK FOR IDENTIFICATION.

CAP.(pf)	TOL.	DC WORKING VOLTAGE		DC CURRENT (AMPS)	I.R. MIN. @ 100 (VDC)	DWV (VDC)	MIN. NO LOAD INSERTION LOSS (db) @ 25°C PER MIL-STD-220				
		85°C	125 °C				1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
5	MAX.	300	200	10	10 G Ω	500	----	----	----	----	----

REVISION RECORD					--TOLERANCES-- Unless Otherwise Specified		Title <b>LINE FEED - THRU</b>			
					DECIMAL ± NOTED					
					ANGLES ± //		Drawn S.M. 02-23-98			
Original Release C.O.					Approved J.Mc. 02-23-98					
WAS SK 7452-000. SM 03-03-98										
<b>19980224-6-02</b>										
ADDED & REVISED NOTES: ADDED IR & DWV. SM 03-03-98										
<b>20060123-9-03</b>										
TUSONIX TUCSON, ARIZONA										
A							<b>4400-682</b>			