

[PRODUCTS](#)
[INDUSTRIES](#)
[CAPABILITIES](#)
[CAREERS](#)
[RESOURCES](#)
[Register](#)
[Login](#)

Home: [Wiring Devices](#) >

Part Number: 130143-0273

Watertite Cordset, 10 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 30.48m (100.0'), NEMA L14-30, 125V/250V



Series image - Reference only

Status:	Active
Series:	130143
Category:	Wiring Devices
Overview:	Watertite Wet-Location Wiring Solutions
EngineeringOldPN:	28W74D104

-
-
-
-

Go to [Part Detail](#) ▼

Specifications & Other Documents:

[Part Details \(PDF\)](#)

Sales Drawings, 3D Models, and Brochures

Note - Please disable browser pop-up blockers to view documents on www.molex.com

Product Environmental Compliance

- [EU ELV](#): Not Reviewed
- [EU RoHS](#): Not Reviewed
- [EU RoHS Phthalates](#): Not Reviewed
- [China RoHS](#): Not Reviewed
- [REACH SVHC](#): Not Reviewed
- [Low-Halogen Status](#): Not Reviewed

-
- EU RoHS, REACH SVHC, & Low-Halogen
- *IPC 1752A Class C
 - *IPC 1752A Class D
 - *Molex Product Compliance Declaration
 - *IEC-62474
 - *chemSHERPA (xml)

View Molex Environmental Position Statements: [Click here](#)

Request Molex's CMRT from conflictminerals@molex.com

Part Detail

-
-
-
-
-

Application Tooling

[FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling

[Check our list of old tooling that used to be available for this part](#)

[Product Categories](#)
[Product Index](#)
[Industries](#)

[Company Information](#)
[Contact Molex](#)
[Cross-Reference](#)
[Koch Industries](#)
[Investor Relations](#)
[Literature](#)
[Press Room / Press Releases](#)
[Sitemap](#)
[Terms & Conditions](#)

[Supply Chain Transparency](#)
[Business Continuity](#)
[Compliance](#)
[ecocare](#)
[Help](#)
[Jobs](#)
[Legal | Trademarks](#)
[Supplier Portal](#)
[Privacy Policy](#)
[Tradeshows](#)



Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2019