N-Channel Power MOSFET – ESD

GENERAL DESCRIPTION

The LT2N7002E is the N-Channel logic enhancement mode power field effect transistors are produced using high cell density, DMOS trench technology. This high density process is especially tailored to minimize on-state resistance. These devices are particularly suited for low voltage application such as cellular phone and notebook computer power management and other battery powered circuits where high-side switching, and low in-line power loss are needed in a very small outline surface mount package.

FEATURES

- Simple Drive Requirement
- Small Package Outline
- ROHS Compliant
- ESD Rating = 2000V HBM

Mechanical data

- High density cell design for low $R_{DS(ON)}$
- Voltage controlled small signal switching.
- Rugged and reliable.
- High saturation current capability.
- High-speed switching.
- Not thermal runaway.
- The soldering temperature and time shall not exceed 260℃ for more than 10 seconds.

PIN CONFIGURATION

(SOT-23)

Top View





Absolute Maximum Ratings (T_A=25℃ Unless Otherwise Noted)

Parameter	Symbol	Ratings	Unit
Drain-Source Voltage	V_{DS}	60	V
Gate-Source Voltage	V_{GS}	±20	V
Continuous Drain Current	I_D	300	mA
Pulsed Drain Current (Note 1)	I_{DM}	2000	mA
Maximum Power Dissipation	P_D @T_A=25°C	0.35	W
	P_D @T_A=75°C	0.21	
Operating Junction and Storage Temperature Range	T_J, Tstg	-55 ~ 150	°C
Junction-to-Ambient Thermal Resistance (PCB mounted) (Note 2)	$R_{\theta JA}$	357	°C/W

Notes：1. Maximum DC current limited by the package

2. Surface mounted on FR4 board, t ≦ 5sec.

N-Channel Power MOSFET – ESD

Electrical Characteristics (T_A=25℃ Unless Otherwise Specified)

Symbol	Parameter	Limit	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	V_{GS}=0, I_D=10uA	60	-	-	V
$V_{GS(th)}$	Gate Threshold Voltage	V_{DS}=V_{GS}, I_D=250uA	1.0	-	2.5	V
g_{fs}	Forward Transconductance	V_{DS}=15V, I_D=250mA	100	-	-	mS
I_{GSS}	Gate Body Leakage	V_{GS}= ±20V , V_{DS}=0V	-	-	±10	uA
I_{DSS}	Zero Gate Voltage Drain Current	V_{DS}=60V, V_{GS}=0V	-	-	1	uA
$R_{DS(ON)}$	Drain-Source On-State Resistance	V_{GS}=10V, I_D=500mA	-	-	3	Ω
		V_{GS}=4.5V, I_D=200mA	-	-	4	
Dynamic						
Q_g	Total Gate Charge	I_D=200mA , V_{DS}=15V V_{GS}=4.5V	-	-	0.8	nC
$T_{d(on)}$	Turn-on Time	V_{DD}=30V , R_L=150Ω, I_D=200mA , V_{GEN}=10V R_G=10Ω	-	-	20	nS
$T_{d(off)}$	Turn-off Time		-	-	40	
C_{iss}	Input Capacitance	V_{GS}=0V V_{DS}=25V f=1.0MHz	-	-	35	pF
C_{oss}	Output Capacitance		-	-	10	
C_{rss}	Reverse Transfer Capacitance		-	-	5	

Source-Drain Diode

Symbol	Parameter	Limit	Min.	Typ.	Max.	Unit
V_{SD}	Diode Forward Voltage	I_S=200mA, V_{GS}=0V	-	0.82	1.3	V

N-Channel Power MOSFET – ESD

Typical Characteristics (T_J =25℃ Noted)

Transfer Characteristics



On-Resistance vs. Drain Current



Output Characteristic



On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage vs. Temperature



On-Resistance vs. Junction Temperature



N-Channel Power MOSFET – ESD

SOT-23 Package Outline



DIM	MILLIMETERS (mm)	
	MIN	MAX
A	2.80	3.00
B	1.20	1.70
C	0.90	1.30
D	0.35	0.50
G	1.78	2.04
H	0.010	0.15
J	0.085	0.20
K	0.30	0.65
L	0.89	1.02
S	2.10	3.00
V	0.45	0.60

Body Marking Code



Important Notice and Disclaimer

LSC reserves the right to make changes to this document and its products and specifications at any time without notice. Customers should obtain and confirm the latest product information and specifications before final design, purchase or use.

LSC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does LSC assume any liability for application assistance or customer product design. LSC does not warrant or accept any liability with products which are purchased or used for any unintended or unauthorized application.

No license is granted by implication or otherwise under any intellectual property rights of LSC.

LSC products are not authorized for use as critical components in life support devices or systems without express written approval of LSC.