



Product Data Sheet

133X554

Replace "x" with 1, 2, or 3 for number of poles
Add suffix "CH" for snap-on hinged cover
Power Terminal Block

310 Amps 600 Volts AC/DC

Wire Range

- Line: (1) 350kcmil - #6 AWG
- Load: (2) 2/0 - #14 AWG

Electrical Ratings

- 310 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- Short circuit current ratings (SCCR): See SCCR section below for specifications.
- CU7AL - 75°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring


Agency Compliance

- UR - UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1


Material Information

- Insulator base:
 - Thermoplastic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 125°C (UL RTI)
- Connector: aluminum, tin plated
- Terminal screws: aluminum, tin plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant

Termination Specifications

Line Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	350 - 300 kcmil	31 N·m (275 lbf·in)	1	B, C
	250 - 2	31 N·m (275 lbf·in)	1	B, C, G, H, I (DLO)
	4 - 6	31 N·m (275 lbf·in)	1	B, C

- Aluminum wire range: 350kcmil - #6
- Wire strip length: 1.0 in. (25mm)
- Terminal screw drive: 5/16 in. hex

Load Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	2/0 - 1/0	13.6 N·m (120 lbf·in)	1	B, C
	1 - 6	13.6 N·m (120 lbf·in)	1	B, C, G, H, I (DLO)
	8	4.5 N·m (40 lbf·in)	1	B, C, G, H, I (DLO)
	10 - 14	4 N·m (35 lbf·in)	1	B, C, I (DLO)

- Solid copper wire range: #10 - 14 AWG
- Aluminum wire range: 2/0 - #8
- Wire strip length: 1.0 in. (25mm)
- Terminal screw drive: 3/16 in. hex

¹ For information on copper stranded wire classes please visit:
<http://www.marathonsp.com/flexible-stranded-wire.php>

Short Circuit Current Ratings (SCCR)

- The suitable conductor ranges are limited to the table values only for achieving the SCCR in excess of the default rating of 10,000A.
- Other conductor combinations within the "Terminal Specifications" noted are suitable for achieving a SCCR of 10,000A (the default rating of terminal blocks).
- Enclosure size – Investigated with a minimum 16x12x6 enclosure. Use in smaller enclosures is subject to end use evaluation.

SCCR With Fuses

Wire Class	Suitable Conductors		Max Overcurrent Protection Fuse Required						SCCR RMS Sym. Amps 600V. Max
			Amp Rating / Class						
	Line	Load	J	T	RK1	RK5	G	CC	
B, C	350 - 3/0	2/0 - 1	500	500	400	200	60	30	100,000
B, C	350 - 6	2/0 - 10	200	200	200	100	60	30	100,000
G, H, I	250 - 1/0	1 - 10	150	150	100	30	60	30	100,000
(*)	350 - 6	2/0 - 14	None						10,000

* Any wire class evaluated (see terminal specification section)

Installation & Accessories

- Mounting (Panel):
 - For use with #10 fastener.
 - Torque mounting fastener to 25-30 lbf·in (2.8 - 3.4 N·m).
- Covers:
 - Snap-on hinge covers available upon request
 - Catalog Number: CH133x (replace "x" with number of poles)
 - Covers are black thermoplastic
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications.

Drawing

