



Main

Range of product	Hyde Park
Sensor type	Ultrasonic sensor
Series name	Superprox +
Device short name	SC300
Sensor design	Flat form
Type of sensing window	Configurable
Material	Plastic
Enclosure material	ULTEM
Front material	Glass epoxy
Type of output signal	Discrete
Wiring technique	4-wire
[Us] rated supply voltage	12...24 V DC (overload and short-circuit protection)
Supply voltage limits	10...28 V DC
Electrical connection	Cable 9.84 ft (3 m)
Product specific application	Discrete proximity

Complementary

Maximum differential travel	0.03 in (0.7 mm)
Blind zone	0.25 in (6.4 mm)
Transmission frequency	500 kHz
Repeat accuracy	0.7 %
Beam angle	8 °
Minimum size of detected object	Cylinder diameter 2.5 mm - up to 1 mm sensing distance
Current consumption	25 mA
Maximum switching current	100 mA (reverse polarity protection)
Height	0.3 in (7.62 mm)
Width	0.75 in (19.05 mm)
Depth	0.3 in (7.62 mm)
Length	1.3 in (33.02 mm)
Product weight	0.26 lb(US) (0.12 kg)

Environment

product certifications	UL
marking	CE
NEMA degree of protection	NEMA 4X (indoor use only)
IP degree of protection	IP67
ambient air temperature for operation	-22...158 °F (-30...70 °C)
ambient air temperature for storage	-40...212 °F (-40...100 °C)
relative humidity	100 % without condensation
vibration resistance	+/-1 mm conforming to IEC 60068-2-6 10...55 Hz
shock resistance	30 gn in all 3 axes 11 ms conforming to IEC 60068-2-27
resistance to electromagnetic fields	9.14 V/yd (10 V/m) (level 3) conforming to IEC 61000-4-3
resistance to fast transients	1 kV (level 3) conforming to IEC 61000-4-4

Contractual warranty

Warranty period	18 months
-----------------	-----------

