



Series: EGP05 • EGP10



Glass Probe NTC Thermistors

EI Sensor's glass probe NTC thermistors offer excellent stability, a fast thermal response and a maximum operating temperature of +300°C. Their glass body is especially suitable for use in harsh environments and corrosive atmospheres.

The accurate temperature measurement and control capabilities of the EI Sensor glass probes makes them a superb choice for applications such as fluid flow, gas flow and liquid level sensing.

The body diameter is 0.069" and there are two body length sizes offered:

EGP05 Series = 0.5" long
EGP10 Series = 1.0" long

To learn more about EI Sensor Thermistors, RTDs, and Probe Assemblies, visit www.ei-sensor.com.

Contact us :

MASTER ELECTRONICS
(888) 473-5297
sales@masterelectronics.com
www.masterelectronics.com

*Many styles in stock for
immediate shipment!*