


# *pico*MAX<sup>®</sup>

The Pluggable Connection System



**WAGO**<sup>®</sup>  
INNOVATIVE CONNECTIONS

TECHNOLOGY THIS RADICAL  
CAN'T MEET ALL REQUIREMENTS.

**YES IT CAN.**

# CONTENTS

## **picoMAX<sup>®</sup>** Pin spacing: 3.5 mm/0.138 in; 5.0 mm/0.197 in; 7.5 mm/0.295 in

Versatile Pluggable Connectors for a Wide Range of Applications

	System Description	2 - 8	
	Handling	9 - 13	
<div style="border: 1px solid green; border-radius: 10px; padding: 10px; text-align: center; width: 150px; margin: 10px auto;"> <span style="font-size: 24px; font-weight: bold; color: green;">3.5</span>  <span style="color: green;">2091 Series</span> </div>	Female Connectors	14 - 17	3.5
	Male Headers with Solder Pins	18 - 20	
	Male Connectors	22 - 23	
	Female Headers with Solder Pins	24 - 25	
	Panel Feedthrough Male Connectors	26 - 27	
<div style="border: 1px solid green; border-radius: 10px; padding: 10px; text-align: center; width: 150px; margin: 10px auto;"> <span style="font-size: 24px; font-weight: bold; color: green;">5.0</span>  <span style="color: green;">2092 Series</span> </div>	Female Connectors	28 - 31	5.0
	Male Headers with Solder Pins	32 - 34	
	Male Connectors	36 - 37	
	Female Headers with Solder Pins	38 - 39	
	Panel Feedthrough Male Connectors	40 - 41	
<div style="border: 1px solid green; border-radius: 10px; padding: 10px; text-align: center; width: 150px; margin: 10px auto;"> <span style="font-size: 24px; font-weight: bold; color: green;">7.5</span>  <span style="color: green;">2092 Series</span> </div>	Female Connectors	42 - 45	7.5
	Male Headers with Solder Pins	46 - 48	
	Male Connectors	50 - 51	
	Female Headers with Solder Pins	52 - 53	

## **picoMAX<sup>®</sup> eCOM** Pin spacing: 3.5 mm/0.138 in; 5.0 mm/0.197 in; 7.5 mm/0.295 in

The Easiest Way to Make PCBs Pluggable

	Description and Handling	54 - 57	
<div style="border: 1px solid green; border-radius: 10px; padding: 10px; text-align: center; width: 150px; margin: 10px auto;"> <span style="font-size: 24px; font-weight: bold; color: green;">3.5</span>  <span style="color: green;">2091 Series</span> </div>	Pin Strip Pluggable Terminal Blocks for Direct Soldering to PCB	58 - 59	3.5
<div style="border: 1px solid green; border-radius: 10px; padding: 10px; text-align: center; width: 150px; margin: 10px auto;"> <span style="font-size: 24px; font-weight: bold; color: green;">5.0</span>  <span style="color: green;">2092 Series</span> </div>	Pin Strip Pluggable Terminal Blocks for Direct Soldering to PCB	60 - 61	5.0
<div style="border: 1px solid green; border-radius: 10px; padding: 10px; text-align: center; width: 150px; margin: 10px auto;"> <span style="font-size: 24px; font-weight: bold; color: green;">7.5</span>  <span style="color: green;">2092 Series</span> </div>	Pin Strip Pluggable Terminal Blocks for Direct Soldering to PCB	62 - 63	7.5
	Accessories	64 - 68	
	Technical Section	70 - 77	
	Index of Item Numbers	78 - 79	
	<b>WAGO Offices</b>	80 - 83	



**A PRODUCT THIS INNOVATIVE CAN'T ALSO BE THIS COMPACT.**

**YES IT CAN.**

The *picoMAX<sup>®</sup>* pluggable connection system has an innovative, **highly compact** design:

- Reduces space by up to 30%
- Minimal space requirements when mated
- The female connector is fully shrouded by the male header's housing.

The *picoMAX<sup>®</sup>* design yields extremely short female connectors. Male headers are equipped with an integrated locking latch.

The **very short contact bridge** separates the clamping unit from the header pin. This creates an **extremely short current path** that minimizes contact resistance.

*picoMAX<sup>®</sup>* is the only pluggable connection system that makes double use of the contact force of **a single stainless steel spring (CrNi)**. One spring, two functions: it applies force to the wire and the header pin at the same time.

The combination of our special design, the **innovative Spring Pressure Connection Technology** and **new insulation material** guarantees **absolute contact reliability** even at high temperatures.



Gripping plate with sliding connector release

Locking tab (on female connector)

Electrolytic copper (E-Cu), tin-plated contact bridge



Push-button

Test port

High-alloy, stainless steel (CrNi) clamping spring

Locking latch (on male header)

Straight or angled, E-Cu, tin-plated solder pins for both wave and THR soldering



Actual size:  
3.5 mm pin spacing

COMPACT

VIBRATION-PROOF

INTUITIVE

UNIVERSAL

EFFICIENT  
Pages 54 - 63




## A PLUGGABLE CONNECTOR CAN'T HANDLE VIBRATIONS UP TO 20g. YES IT CAN.

The *picoMAX<sup>®</sup>* pluggable connection system has an innovative, **extremely vibration-proof** design: The protruding **locking tabs** of the female connector **interlock** with the **locking latch** of the male header, for a secure connection. This allows the female connector to be **automatically locked in place**, while being almost fully shrouded by the male header.

The clamping point of the terminated conductor and the contact point of the inserted header pin are virtually opposite each other. This unique configuration provides **uniform mass distribution**, making *picoMAX<sup>®</sup>* connectors ideal for vibration-prone applications. The **contact force** between conductor, contact bridge and header pin is dynamic – it **automatically adjusts** to the conductor size.

This also allows *picoMAX<sup>®</sup>* wire-to-board connections to achieve high contact reliability even when subjected to vibrations of **up to 20 g** based on IEC 60068-2-6.

Its shortened connector also means *picoMAX<sup>®</sup>* has a lower center of gravity, closer to the PCB. These features turn *picoMAX<sup>®</sup>* into the **new standard for vibration-proof pluggable connector systems**.



- Locking latch  
(on male header)
- Locking tab  
(on female connector)
- Contact bridge
- E-Cu, tin-plated  
header pin

COMPACT

VIBRATION-PROOF

INTUITIVE

UNIVERSAL

EFFICIENT  
Pages 54 - 63



## A CONNECTOR WITH THIS MANY FEATURES CAN'T BE INTUITIVE TO USE. YES IT CAN.

The *picoMAX*<sup>®</sup> pluggable connection system is intuitive and easy to use – worldwide:

### **Fast conductor termination**

- Push-in termination of solid or ferruled conductors
- Easy push-button actuation – for termination of stranded conductors and for removal of all conductor types
- Can be terminated in mated or unmated condition

### **Integrated locking latches**

- Prevent accidental disconnection of male header and female connector

### **Easy disconnection**

- Via easy-to-use sliding connector release on gripping plate
- Using convenient unlocking tool (for applications without gripping plate)

### **Efficient testing**


- Via test port, parallel to conductor entry
- Even when mated and wired

### **Grouping connectors without losing poles**

- Within one male header housing
- E.g., group 2x 4-pole female connectors in 1x 8-pole male header

### **Easy panel feedthrough connections**

- E.g., to pass through an enclosure wall with plug-in option on both sides



Integrated push-button

Gripping plate with sliding connector release for fast and tool-free disconnection

Test port, parallel to conductor entry

Integrated locking latch

COMPACT

VIBRATION-PROOF


INTUITIVE

UNIVERSAL

EFFICIENT  
Pages 54 - 63





























# *pico*MAX<sup>®</sup>

The Pluggable Connection System



# picoMAX® Pluggable Connectors

Combination Overview for Male and Female Connectors/Headers  
 Pin Spacing: 3.5 mm/0.138 in; 5.0 mm/0.197 in; 7.5 mm/0.295 in

		Male Connectors/Headers					
		Header with straight solder pins	Header with angled solder pins	Connector and integrated release lever	Panel feedthrough connector		
					Outside 	Inside (unlocked) 	
Female Connectors/Headers	Connector and gripping plate with sliding connector release 				Outside 	Inside 	
Connector and gripping plate 	 	 	 	Outside  	Inside  		
Connector 	 	 	 	Outside  	Inside  		
Header with straight solder pins 				Outside 	Inside 		
Header with angled solder pins 				Outside 	Inside 		



Disconnection: Open locking latches via unlocking tool.

COMPACT

VIBRATION-PROOF


INTUITIVE

UNIVERSAL


EFFICIENT  
Pages 54 - 63



## Touch-Proof PCB Output: "Board-to-Wire"




## "Wire-to-Wire" Flying Lead






## "Wire-to-Board" Panel Feedthrough



## "Wire-to-Wire" Panel Feedthrough




# Handling *picoMAX*<sup>®</sup>

Pin Spacing: 3.5 mm/0.138 in; 5.0 mm/0.197 in; 7.5 mm/0.295 in



Inserting stranded conductor into unmated female connector via push-button.




Inserting stranded conductor into mated female connector via push-button.




Inserting solid and ferruled conductors via push-in termination.




Easy-to-identify PCB inputs and outputs.



The locking latch of the male header interlocks with the locking tab of the female connector, for a secure connection.



"Wire-to-wire" flying leads with optional gripping plates



Male connectors with snap-in mounting feet for panel mounting.



Male connector with snap-in mounting feet on mounting adapter for DIN 35 rail.



Pole marking via factory direct printing.



**CAGE CLAMP<sup>®</sup> S**  
clamps the following  
copper conductors:

solid




stranded




fine-stranded,  
also with finned  
single strands





Male header mated to a female connector with gripping plate and sliding connector release.



Disconnecting female connector via sliding connector release.  
**1** Push down sliding connector release (on gripping plate) to open the locking latch.  
**2** Pull out female connector from male header.



Disconnecting female connector via unlocking tool. Plug unlocking tool into the male locking latch.




Insert unlocking tool until it hits backstop. Wedge opens locking latches.




Pull on both unlocking tool and conductors to remove female connector from male header.



Coding a female connector (via coding key carrier and two keys for female connector, see symbol).



Coding a male header (via coding key carrier and two keys for male header, see symbol).



Unlocking tool may be suspended on wire harness for storage.




fine-stranded, tip-bonded



fine-stranded, with ferrule (gastight crimped)

# Female Connectors

## picoMAX® 3.5



- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Ability to wire while mated or unmated
- Testing port parallel to conductor entry – tip contact
- Integrated locking latches prevent accidental disconnection

### Technical data:

Pin Spacing	3.5 mm 0.138 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	160 V	320 V
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV
Nominal current	10 A	10 A	10 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	10	-	10
Nominal current CSA	-	-	-


### Conductor data:

Connection technology	CAGE CLAMP® S
Conductor size: solid	0.2 - 1.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.2 - 1.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.25 - 0.75 mm <sup>2</sup> (with insulated ferrule)
Conductor size: fine-stranded	0.25 - 1.5 mm <sup>2</sup> (with uninsulated ferrule)
AWG	24 - 14 (2.8 mm max. outside diameter)
Strip length	8 - 9 mm / 0.31 - 0.35 in

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>cu</sub> )
Contact plating	tin-plated

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



For additional derating curves, see page 71.

### Accessories for picoMAX®:

### Page:

Operating tools	64
Direct printing	68
Gripping plates	65
Coding pins	66
Test probe	64




Approvals are available online at: [www.wago.com](http://www.wago.com) \*CSA approval pending  
For more technical information, see Full Line Catalog, Volume 2, Section 11

# Female Connectors picoMAX® 3.5

<b>With gripping plate and sliding connector release</b> <b>Pin spacing: 3.5 mm / 0.138 in</b> 0.2 - 1.5 mm <sup>2</sup>   AWG 24 - 14 160 V/2.5 kV/2 10 A   300 V/10 A		<b>Mates with:</b>
----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	--	--------------------



3.5





L = pole no. x pin spacing

Pole No.	Item No.	Pack. Unit
<b>Female connector with gripping plate and sliding connector release, light gray</b>		
2	2091-1102/002-000	100
3	2091-1103/002-000	100
4	2091-1104/002-000	100
5	2091-1105/002-000	50
6	2091-1106/002-000	50
8	2091-1108/002-000	50
10	2091-1110/002-000	50
12	2091-1112/002-000	50

**Gripping plate dimensions (in mm):**

Pole No.	A	B	C	D	E
2	6	2.00	-	17	-
3	6	2.25	-	17	-
4	6	2.25	-	17	-
5	13	2.25	3.0	20	5
6	13	2.25	3.0	20	5
8	13	5.75	3.0	20	5
10	27	2.25	4.2	25	8
12	27	5.75	4.2	25	8



Female connector mated to a male header with gripping plate and sliding connector release.



Push down sliding connector release (gripping plate) to open the locking latch.




Pull out female connector with gripping plate from male header.



# Female Connectors picoMAX® 3.5

CAGE CLAMP® S

<p>With gripping plate Pin spacing: 3.5 mm / 0.138 in</p>		<p>Mates with:</p>
<p>0.2 – 1.5 mm<sup>2</sup> 160 V/2.5 kV/2 10 A</p>	<p>AWG 24 – 14 300 V/10 A</p>	



L = pole no. x pin spacing

Pole No.	Item No.	Pack. Unit
<b>Female connector with gripping plate, light gray</b>		
2	2091-1102	100
3	2091-1103	100
4	2091-1104	100
5	2091-1105	50
6	2091-1106	50
8	2091-1108	50
10	2091-1110	50
12	2091-1112	50
<b>Product Accessories</b>		<b>Page</b>
Unlocking tool (2092-1630)		64

### Gripping plate dimensions (in mm):

Pole No.	A	B	C	D	E
2	3	2.00	-	17	-
3	6	2.25	-	17	-
4	6	2.25	-	17	-
5	13	2.25	3.0	20	5
6	13	2.25	3.0	20	5
8	13	5.75	3.0	20	5
10	27	2.25	4.2	25	8
12	27	5.75	4.2	25	8

Header with straight solder pins

Header with angled solder pins

Male connector

Panel feedthrough connector

**Outside**

**Inside**


Disconnection: Open locking latches via unlocking tool.



Disconnecting female connector via unlocking tool. Plug unlocking tool into the male header's locking latch.



Insert unlocking tool until it hits backstop. Wedge opens locking latch.




Pull on both unlocking tool and conductors to remove female connector from male header.

# Female Connectors picoMAX® 3.5

<b>Pin spacing: 3.5 mm / 0.138 in</b>		<b>Mates with:</b>
0.2 – 1.5 mm <sup>2</sup> 160 V/2.5 kV/2 10 A	AWG 24 – 14 300 V/10 A	



3.5



L = pole no. x pin spacing

Pole No.	Item No.	Pack. Unit
<b>Female connector, light gray</b>		
2	2091-1122	200
3	2091-1123	200
4	2091-1124	200
5	2091-1125	200
6	2091-1126	100
8	2091-1128	100
10	2091-1130	100
12	2091-1132	100
<b>Product Accessories</b>		<b>Page</b>
Unlocking tool (2092-1630)		64

Header with straight solder pins

✓

Header with angled solder pins

✓

Male connector

✓

Panel feedthrough connector

Outside

Inside

✓

Disconnection: Open locking latches via unlocking tool.



Disconnecting female connector via unlocking tool. Plug unlocking tool into the male header's locking latch.




Insert unlocking tool until it hits backstop. Wedge opens locking latch.



Pull on both unlocking tool and conductors to remove female connector from male header.

# Male Headers with Solder Pins

## picoMAX® 3.5



- Horizontal or vertical plug direction via straight or angled solder pins
- Group female connectors without loss of poles, allowing different functions to be divided within one male header
- Coding pins inserted into the header interface prevent mismatching, allowing subsequent coding in panel feedthrough applications
- Female connector is almost fully shrouded by the male header, providing vibration-resistance up to 20 g\*

### Technical data:

Pin Spacing	3.5 mm 0.138 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	160 V	320 V
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV
Nominal current	10 A	10 A	10 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA**		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	10	-	10
Nominal current CSA	-	-	-

### Solder pin data for THT (wave soldering):

Solder pin: length/width	3.6 mm / 1.0 mm Ø
Solder pin: drilled hole diameter	1.2 <sup>+0.1</sup> mm


### Solder pin data for THR\*\*\* (reflow soldering):

Solder pin: length/width	2.4 mm / 1.0 mm Ø
Solder pin: metal-plated hole	1.2 <sup>+0.1</sup> mm Ø

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



For additional derating curves, see page 71.

### Accessories for picoMAX®:

Page:

Coding pins	66







# Male Headers with Solder Pins

## picoMAX® 3.5

With straight solder pins Pin spacing: 3.5 mm / 0.138 in		With angled solder pins Pin spacing: 3.5 mm / 0.138 in		Mates with:
160 V/2.5 kV/2 10 A	300 V/10 A	160 V/2.5 kV/2 10 A	300 V/10 A	



3.5





L = (pole no. x pin spacing) + 2 mm  
 A = 3.6 mm (THT solder pin)  
 A = 2.4 mm (THR solder pin)

Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
Male header with straight solder pins, light gray			Male header with angled solder pins, light gray		
2	2091-1402	200	2	2091-1422	200
3	2091-1403	200	3	2091-1423	200
4	2091-1404	200	4	2091-1424	200
5	2091-1405	200	5	2091-1425	200
6	2091-1406	100	6	2091-1426	100
8	2091-1408	100	8	2091-1428	100
10	2091-1410	100	10	2091-1430	100
12	2091-1412	100	12	2091-1432	100

Item no. suffix for colored THR version:



○ light gray	...../200-000	<b>Ordering example:</b>
THR male headers with solder pins in tape-and-reel packaging available upon request		THR male header with straight solder pins, 3.5 mm pin spacing, 8-pole, light gray: <b>2091-1408/200-000</b>



Disconnection: Open locking latches via unlocking tool.

# Male Headers with Solder Pins and Fixing Flanges picoMAX® 3.5

<b>With straight solder pins and fixing flanges</b> <b>Pin spacing: 3.5 mm / 0.138 in</b>		<b>With angled solder pins and fixing flanges</b> <b>Pin spacing: 3.5 mm / 0.138 in</b>		<b>Mates with:</b>
160 V/2.5 kV/2 10 A	300 V/10 A	160 V/2.5 kV/2 10 A	300 V/10 A	



$L = (\text{pole no.} \times \text{pin spacing}) + 2 \text{ mm}$   
 $L_1 = (\text{pole no.} \times \text{pin spacing}) + 7.8 \text{ mm}$   
 $L_2 = (\text{pole no.} \times \text{pin spacing}) + 6.8 \text{ mm}$   
 $A = 3.6 \text{ mm (THT solder pin)}$   
 $A = 2.4 \text{ mm (THR solder pin)}$

Female connector and gripping plate with sliding connector release

Female connector and gripping plate

Female connector

Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
Male header with straight solder pins and fixing flanges, light gray			Male header with angled solder pins and fixing flanges, light gray		
2	2091-1402/005-000	200	2	2091-1422/005-000	200
3	2091-1403/005-000	200	3	2091-1423/005-000	200
4	2091-1404/005-000	200	4	2091-1424/005-000	200
5	2091-1405/005-000	200	5	2091-1425/005-000	200

Disconnection: Open locking latches via unlocking tool.


Item no. suffix for colored THR version:

○ light gray	...../205-000	<b>Ordering example:</b>
THR male headers with solder pins in tape-and-reel packaging available upon request		THR male header with straight solder pins and fixing flanges, 3.5 mm pin spacing, 5-pole, light gray: <b>2091-1405/205-000</b>



# Male Connectors

## picoMAX® 3.5



- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Easy-to-use design does not require specialty tools
- Testing port parallel to conductor entry – tip contact
- For “wire-to-wire” and “board-to-wire” connections
- Integrated release lever
- Also available with gripping plates

### Technical data:

Pin Spacing	3.5 mm 0.138 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	160 V	320 V
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV
Nominal current	10 A	10 A	10 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	10	-	10
Nominal current CSA	-	-	-


### Conductor data:

Connection technology	CAGE CLAMP® S
Conductor size: solid	0.2 - 1.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.2 - 1.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.25 - 0.75 mm <sup>2</sup> (with insulated ferrule)
Conductor size: fine-stranded	0.25 - 1.5 mm <sup>2</sup> (with uninsulated ferrule)
AWG	24 - 14 (2.8 mm max. outside diameter)
Strip length	8 - 9 mm / 0.31 - 0.35 in

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



For additional derating curves, see page 71.

### Accessories for picoMAX®:

### Page:

Operating tools	64
Direct printing	68
Gripping plates	65
Coding pins	66
Test probe	64




# Male Connectors picoMAX® 3.5

CAGE CLAMP® S

Pin spacing: 3.5 mm / 0.138 in		With gripping plate Pin spacing: 3.5 mm / 0.138 in		With snap-in mounting feet Pin spacing: 3.5 mm / 0.138 in	
0.2 - 1.5 mm <sup>2</sup>	AWG 24 - 14	0.2 - 1.5 mm <sup>2</sup>	AWG 24 - 14	0.2 - 1.5 mm <sup>2</sup>	AWG 24 - 14
160 V/2.5 kV/2 10 A	300 V/10 V	160 V/2.5 kV/2 10 A	300 V/10 A	160 V/2.5 kV/2 10 A	300 A/10 A



3.5




L = (pole no. x pin spacing) + 2 mm  
 Even pole number R = (L - 9 mm) : 2  
 Odd pole number R = (L - 12.5 mm) : 2

Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
Male connector, light gray			Male connector with gripping plate, light gray			Male connector with snap-in mounting feet, for 0.6 - 1.2 mm plate thickness, light gray		
2	2091-1522/002-000	200	2	2091-1502/002-000	200	2	2091-1522/020-000	200
4	2091-1524/002-000	200	4	2091-1504/002-000	100	4	2091-1524/020-000	200
6	2091-1526/002-000	100	6	2091-1506/002-000	50	6	2091-1526/020-000	100
8	2091-1528/002-000	100	8	2091-1508/002-000	50	8	2091-1528/020-000	100

Product Accessories	Page
Mounting adapter for DIN 35 rail, 3 or more poles (209-189)	66

### Gripping plate dimensions (in mm):


Pole No.	A	B	C	D	E
2	6	3	-	17	-
4	6	3.25	-	17	-
6	13	3.25	3	20	5
8	13	6.75	3	20	5



Standard male connectors can be combined with any female connectors/headers.

# Female Headers with Solder Pins

## picoMAX® 3.5



- Horizontal or vertical plug direction via straight or angled solder pins
- Touch-proof PCB outputs
- Easy-to-identify PCB inputs and outputs
- Coding pins available

### Technical data:

Pin Spacing	3.5 mm 0.138 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	160 V	320 V
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV
Nominal current	10 A	10 A	10 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	10	-	10
Nominal current CSA	-	-	-

### Solder pin data for THT (wave soldering):

Solder pin: length/width	3.6 mm / 0.4 x 0.9 mm
Solder pin: drilled hole diameter	1.1 <sup>+0.1</sup> mm


### Solder pin data for THR\*\* (reflow soldering):

Solder pin: length/width	2.4 mm / 0.4 x 0.9 mm
Solder pin: metal-plated hole	1.1 <sup>+0.1</sup> mm Ø

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Contact material	Copper alloy
Contact plating	tin-plated

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



For additional derating curves, see page 71.

### Accessories for picoMAX®:

Page:

Coding pins	66



# Female Headers with Solder Pins

## picoMAX® 3.5


With straight solder pins Pin spacing: 3.5 mm / 0.138 in		With angled solder pins Pin spacing: 3.5 mm / 0.138 in		Mates with:
160 V/2.5 kV/2 10 A	300 V/10 A	160 V/2.5 kV/2 10 A	300 V/10 A	



3.5



L = pole no. x pin spacing  
 A = 3.6 mm (THT solder pin)  
 A = 2.4 mm (THR solder pin)




Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
Female header with straight solder pins, light gray			Female header with angled solder pins, light gray		
2	2091-1302	200	2	2091-1322	200
4	2091-1304	200	4	2091-1324	200
6	2091-1306	100	6	2091-1326	100
8	2091-1308	100	8	2091-1328	100

Item no. suffix for colored THR version:

○ light gray	...../200-000	<b>Ordering example:</b>
THR female headers with solder pins in tape-and-reel packaging available upon request		THR female header with straight solder pins, 3.5 mm pin spacing, 8-pole, light gray: <b>2091-1308/200-000</b>

# Panel Feedthrough Male Connectors with Fixing Flanges


## picoMAX® 3.5



- Male connectors for screw mounting in device or enclosure panels
- External plug-in connection to standard female connector via integrated locking latches
- Internal plug-in connection to female header with solder pins or standard female connector
- Fixing flanges also suitable for panel mounting

### Technical data:

Pin Spacing	3.5 mm 0.138 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	160 V	320 V
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV
Nominal current	10 A	10 A	10 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	10	-	10
Nominal current CSA	-	-	-



For additional derating curves, see page 71.

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated

### Accessories for picoMAX®:

### Page:


Operating tools	64
Coding pins	66
Test probe	64

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.





# Female Connectors picoMAX® 5.0



- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Ability to wire while mated or unmated
- Testing port parallel to conductor entry – tip contact
- Integrated locking latches prevent accidental disconnection

### Technical data:

Pin Spacing	5 mm 0.197 in		
Ratings per	IEC/EN 60664-1		
Overtoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250 V	320 V	630 V
Rated surge voltage	4 kV	4 kV	4 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-


### Conductor data:

Connection technology	CAGE CLAMP® S
Conductor size: solid	0.2 - 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.2 - 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.25 - 1.5 mm <sup>2</sup> (with insulated ferrule)
Conductor size: fine-stranded	0.25 - 2.5 mm <sup>2</sup> (with uninsulated ferrule)
AWG	24 - 12 (4.1 mm max. outside diameter)
Strip length	9 - 10 mm / 0.35 - 0.39 in

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>cu</sub> )
Contact plating	tin-plated

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



For additional derating curves, see page 72.

### Accessories for picoMAX®:

### Page:


Operating tools	64
Direct printing	68
Gripping plates	65
Coding pins	66
Test probe	64



Approvals are available online at: [www.wago.com](http://www.wago.com) \*CSA approval pending  
For more technical information, see Full Line Catalog, Volume 2, Section 11

# Female Connectors picoMAX® 5.0

<b>With gripping plate and sliding connector release</b> <b>Pin spacing: 5 mm / 0.197 in</b> 0.2 – 2.5 mm <sup>2</sup>   AWG 24 – 12 320 V/4 kV/2 16 A   300 V/15 A		<b>Mates with:</b>	
------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	--	--------------------	--




L = pole no. x pin spacing

Pole No.	Item No.	Pack. Unit
<b>Female connector with gripping plate and sliding connector release, light gray</b>		
2	2092-1102/002-000	100
3	2092-1103/002-000	100
4	2092-1104/002-000	100
5	2092-1105/002-000	50
6	2092-1106/002-000	50
8	2092-1108/002-000	50
10	2092-1110/002-000	50
12	2092-1112/002-000	50

**Gripping plate dimensions (in mm):**

Pole No.	A	B	C	D	E
2	7	1.5	-	20	-
3	12	1.5	-	20	-
4	12	1.5	-	20	-
5	22	1.5	3.5	25	9
6	22	1.5	3.5	25	9
8	22	6.5	3.5	25	9
10	42	1.5	5.0	35	19
12	42	6.5	5.0	35	19



Female connector mated to a male header with gripping plate and sliding connector release.



Push down sliding connector release (gripping plate) to open the locking latch.




Pull out female connector with gripping plate from male header.

5.0

# Female Connectors picoMAX® 5.0

CAGE CLAMP® S

<p>With gripping plate Pin spacing: 5 mm / 0.197 in</p>		<p>Mates with:</p>
<p>0.2 - 2.5 mm<sup>2</sup> 320 V/4 kV/2 16 A</p>	<p>AWG 24 - 12 300 V/15 A</p>	



L = pole no. x pin spacing

Pole No.	Item No.	Pack. Unit
<b>Female connector with gripping plate, light gray</b>		
2	2092-1102	100
3	2092-1103	100
4	2092-1104	100
5	2092-1105	50
6	2092-1106	50
8	2092-1108	50
10	2092-1110	50
12	2092-1112	50
<b>Product Accessories</b>		<b>Page</b>
Unlocking tool (2092-1630)		64

**Gripping plate dimensions (in mm):**

Pole No.	A	B	C	D	E
2	7	1.5	-	20	-
3	12	1.5	-	20	-
4	12	1.5	-	20	-
5	22	1.5	3.5	25	9
6	22	1.5	3.5	25	9
8	22	6.5	3.5	25	9
10	42	1.5	5.0	35	19
12	42	6.5	5.0	35	19

Header with straight solder pins

Header with angled solder pins


Male connector

Panel feedthrough connector

**Outside**

**Inside**


Disconnection: Open locking latches via unlocking tool.



Disconnecting female connector via unlocking tool. Plug unlocking tool into the male header's locking latch.



Insert unlocking tool until it hits backstop. Wedge opens locking latch.




Pull on both unlocking tool and conductors to remove female connector from male header.

# Female Connectors picoMAX® 5.0




CAGE CLAMP® S

Pin spacing 5 mm / 0.197 in		Mates with:
0.2 – 2.5 mm <sup>2</sup> 320 V/4 kV/2 16 A	AWG 24 – 12 300 V/15 A	



L = pole no. x pin spacing

Pole No.	Item No.	Pack. Unit
<b>Female connector, light gray</b>		
2	2092-1122	200
3	2092-1123	200
4	2092-1124	200
5	2092-1125	200
6	2092-1126	100
8	2092-1128	100
10	2092-1130	100
12	2092-1132	100
<b>Product Accessories</b>		<b>Page</b>
Unlocking tool (2092-1630)		64



Disconnecting female connector via unlocking tool. Plug unlocking tool into the male header's locking latch.



Insert unlocking tool until it hits backstop. Wedge opens locking latch.




Pull on both unlocking tool and conductors to remove female connector from male header.

5.0

# Male Headers with Solder Pins

## picoMAX® 5.0



- Horizontal or vertical plug direction via straight or angled solder pins
- Group female connectors without loss of poles, allowing different functions to be divided within one male header
- Coding pins inserted into the header interface prevent mismatching, allowing subsequent coding in panel feedthrough applications
- Female connector is almost fully shrouded by the male header, providing vibration-resistance up to 20 g\*

### Technical data:

Pin Spacing	5 mm 0.197 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250 V	320 V	630 V
Rated surge voltage	4 kV	4 kV	4 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA**		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-

### Solder pin data for THT (wave soldering):

Solder pin: length/width	3.6 mm / 1.4 mm Ø
Solder pin: drilled hole diameter	1.6 <sup>+0.1</sup> mm


### Solder pin data for THR\*\* (reflow soldering):

Solder pin: length/width	2.4 mm / 1.4 mm Ø
Solder pin: metal-plated hole	1.6 <sup>+0.1</sup> mm Ø

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



For additional derating curves, see page 72.

### Accessories for picoMAX®:

Page:

Coding pins	66





Approvals are available online at: [www.wago.com](http://www.wago.com) \*Testing based on IEC 60068-2-6 \*\*CSA approval pending  
\*\*\*For THR soldering, see page 69 For more technical information, see Full Line Catalog, Volume 2, Section 11



# Male Headers with Solder Pins

## picoMAX® 5.0

With straight solder pins Pin spacing: 5 mm / 0.197 in		With angled solder pins Pin spacing: 5 mm / 0.197 in		Mates with:
320 V/4 kV/2 16 A	300 V/15 A	320 V/4 kV/2 16 A	300 V/15 A	





L = (pole no. x pin spacing) + 2.2 mm  
 A = 3.6 mm (THT solder pin)  
 A = 2.4 mm (THR solder pin)

Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
<b>Male header with straight solder pins,</b> light gray			<b>Male header with angled solder pins,</b> light gray		
2	2092-1402	200	2	2092-1422	200
3	2092-1403	200	3	2092-1423	200
4	2092-1404	200	4	2092-1424	200
5	2092-1405	200	5	2092-1425	200
6	2092-1406	100	6	2092-1426	100
8	2092-1408	100	8	2092-1428	100
10	2092-1410	100	10	2092-1430	100
12	2092-1412	100	12	2092-1432	100

Item no. suffix for colored THR version:

○ light gray	...../200-000	<b>Ordering example:</b>
THR male headers with solder pins in tape-and-reel packaging available upon request		THR male header with straight solder pins, 5 mm pin spacing, 8-pole, light gray: <b>2092-1408/200-000</b>





Disconnection: Open locking latches via unlocking tool.

5.0




# Male Headers with Solder Pins and Fixing Flanges picoMAX® 5.0

With straight solder pins and fixing flanges Pin spacing: 5 mm / 0.197 in		With angled solder pins and fixing flanges Pin spacing: 5 mm / 0.197 in		Mates with:
320 V/4 kV/2 16 A	300 V/15 A	320 V/4 kV/2 16 A	300 V/15 A	




$L = (\text{pole no.} \times \text{pin spacing}) + 2.2 \text{ mm}$   
 $L_1 = (\text{pole no.} \times \text{pin spacing}) + 8 \text{ mm}$   
 $L_2 = (\text{pole no.} \times \text{pin spacing}) + 7 \text{ mm}$   
 $A = 3.6 \text{ mm}$  (THT solder pin)  
 $A = 2.4 \text{ mm}$  (THR solder pin)




Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
Male header with straight solder pins and fixing flanges, light gray			Male header with angled solder pins and fixing flanges, light gray		
2	2092-1402/005-000	200	2	2092-1422/005-000	200
3	2092-1403/005-000	200	3	2092-1423/005-000	200
4	2092-1404/005-000	200	4	2092-1424/005-000	200
5	2092-1405/005-000	200	5	2092-1425/005-000	200

Item no. suffix for colored THR version:

○ light gray	...../205-000	<b>Ordering example:</b>
THR male headers with solder pins in tape-and-reel packaging available upon request		THR male header with straight solder pins and fixing flanges, 5 mm pin spacing, 5-pole, light gray: <b>2092-1405/205-000</b>






5.0

# Male Connectors

## picoMAX® 5.0



- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Easy-to-use design does not require specialty tools
- Testing port parallel to conductor entry – tip contact
- For “wire-to-wire” and “board-to-wire” connections
- Integrated release lever
- Also available with gripping plates

### Technical data:


Pin Spacing	5 mm 0.197 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250 V	320 V	630 V
Rated surge voltage	4 kV	4 kV	4 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-

### Conductor data:

Connection technology	CAGE CLAMP® S
Conductor size: solid	0.2 – 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.2 – 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.25 – 1.5 mm <sup>2</sup> (with insulated ferrule)
Conductor size: fine-stranded	0.25 – 2.5 mm <sup>2</sup> (with uninsulated ferrule)
AWG	24 – 12 (4.1 mm max. outside diameter)
Strip length	9 – 10 mm / 0.35 – 0.39 in

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated



For additional derating curves, see page 72.




### Accessories for picoMAX®:

### Page:

Gripping plates	65
Coding pins	66
Test probe	64

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

Pin spacing: 5 mm / 0.197 in		With gripping plate Pin spacing: 5 mm / 0.197 in		With snap-in mounting feet Pin spacing: 5 mm / 0.197 in	
0.2 - 2.5 mm <sup>2</sup> 320 V/4 kV/2 16 A	AWG 24 - 12 300 V/15 A	0.2 - 2.5 mm <sup>2</sup> 320 V/4 kV/2 16 A	AWG 24 - 12 300 V/15 A	0.2 - 2.5 mm <sup>2</sup> 320 V/4 kV/2 16 A	AWG 24 - 12 300 V/15 A



L = (pole no. x pin spacing) + 2.2 mm  
 Even pole number R = (L - 12 mm) : 2  
 Odd pole number R = (L - 17 mm) : 2


5.0

Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
<b>Male connector, light gray</b>			<b>Male connector with gripping plate, light gray</b>			<b>Male connector with snap-in mounting feet, light gray</b>		
for 0.6 - 1.2 mm plate thickness,						for 0.6 - 1.2 mm plate thickness,		
2	2092-1522/002-000	200	2	2092-1502/002-000	100	2	2092-1522/020-000	200
3	2092-1523/002-000	100	3	2092-1503/002-000	100	3	2092-1523/020-000	100
4	2092-1524/002-000	100	4	2092-1504/002-000	50	4	2092-1524/020-000	100
5	2092-1525/002-000	100	5	2092-1505/002-000	50	5	2092-1525/020-000	100
6	2092-1526/002-000	100	6	2092-1506/002-000	50	6	2092-1526/020-000	50

Product Accessories	Page
Mounting adapter for DIN 35 rail, 3 or more poles (209-189)	66

**Gripping plate dimensions (in mm):**


Pole No.	A	B	C	D	E
2	7	2.6	-	20	-
3	12	2.6	-	20	-
4	12	2.6	-	20	-
5	22	2.6	3.5	25	9
6	22	2.6	3.5	25	9



Standard male connectors can be combined with any female connectors/headers.

# Female Headers with Solder Pins

## picoMAX® 5.0



- Horizontal or vertical plug direction via straight or angled solder pins
- Touch-proof PCB outputs
- Easy-to-identify PCB inputs and outputs
- Coding pins available

### Technical data:

Pin Spacing	5 mm 0.197 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250 V	320 V	630 V
Rated surge voltage	4 kV	4 kV	4 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-

### Solder pin data for THT (wave soldering):

Solder pin: length/width	3.6 mm / 0.4 x 1.3 mm
Solder pin: drilled hole diameter	1.5 <sup>+0.1</sup> mm


### Solder pin data for THR\*\* (reflow soldering):

Solder pin: length/width	2.4 mm / 0.4 x 1.3 mm
Solder pin: metal-plated hole	1.5 <sup>+0.1</sup> mm Ø

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Contact material	Copper alloy
Contact plating	tin-plated

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



For additional derating curves, see page 72.

### Accessories for picoMAX®:



### Page:

Coding pins	66


# Female Headers with Solder Pins

## picoMAX® 5.0

With straight solder pins Pin spacing: 5 mm / 0.197 in		With angled solder pins Pin spacing: 5 mm / 0.197 in		Mates with:
320 V/4 kV/2 16 A	300 V/15 A	320 V/4 kV/2 16 A	300 V/15 A	



L = pole no. x pin spacing  
 A = 3.6 mm (THT solder pin)  
 A = 2.4 mm (THR solder pin)



Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
Female header with straight solder pins, light gray			Female header with angled solder pins, light gray		
2	2092-1302	200	2	2092-1322	200
3	2092-1303	200	3	2092-1323	200
4	2092-1304	200	4	2092-1324	200
5	2092-1305	100	5	2092-1325	100
6	2092-1306	100	6	2092-1326	100

### Item no. suffix for colored THR version:

○ light gray	...../200-000	<b>Ordering example:</b>
THR female headers with solder pins in tape-and-reel packaging available upon request		THR female header with straight solder pins, 5 mm pin spacing, 8-pole, light gray: <b>2092-1308/200-000</b>

5.0

# Panel Feedthrough Male Connectors with Fixing Flanges


## picoMAX® 5.0



- Male connectors for screw mounting in device or enclosure panels
- External plug-in connection to standard female connector via integrated locking latches
- Internal plug-in connection to female header with solder pins or standard female connector
- Fixing flanges also suitable for panel mounting

### Technical data:

Pin Spacing	5 mm 0.197 in		
	IEC/EN 60664-1		
Ratings per	III	III	II
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250 V	320 V	630 V
Rated surge voltage	4 kV	4 kV	4 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-



For additional derating curves, see page 72.

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Contact material	Electrolytic copper (E <sub>cu</sub> )
Contact plating	tin-plated

### Accessories for picoMAX®:

### Page:



Operating tools	64
Coding pins	66
Test probe	64

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



# Panel Feedthrough Male Connectors with Fixing Flanges picoMAX® 5.0

Pin spacing: 5 mm / 0.197 in	Mates with:	Applications
320 V/4 kV/2 16 A	300 V/15 A	



$L = (\text{pole no.} \times \text{pin spacing}) + 2.2 \text{ mm}$   
 $L_1 = (\text{pole no.} \times \text{pin spacing}) + 8 \text{ mm}$   
 $L_2 = (\text{pole no.} \times \text{pin spacing}) + 7 \text{ mm}$

Pole No.	Item No.	Pack. Unit
<b>Panel feedthrough male connector with fixing flanges, light gray</b>		
2	2092-1632/024-000	100
3	2092-1633/024-000	100
4	2092-1634/024-000	50
5	2092-1635/024-000	50
6	2092-1636/024-000	50

Female connector and gripping plate with sliding connector release

Outside  Inside



"Wire-to-wire" panel feedthrough connection  
Notice: Male connectors shall not be live when disconnected!

Female connector and gripping plate

Outside  Inside



"Wire-to-board" panel feedthrough connection

Female connector

Outside  Inside

Header with straight or angled solder pins


Outside  Inside

Disconnection: Open locking latches via unlocking tool.

5.0

# Female Connectors

## picoMAX® 7.5



- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Ability to wire while mated or unmated
- Testing port parallel to conductor entry – tip contact
- Integrated locking latches prevent accidental disconnection

### Technical data:

Pin Spacing	7.5 mm 0.295 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	400 V	630 V	1000 V
Rated surge voltage	6 kV	6 kV	6 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-


### Conductor data:

Connection technology	CAGE CLAMP® S	
Conductor size: solid	0.2 - 2.5 mm <sup>2</sup>	
Conductor size: fine-stranded	0.2 - 2.5 mm <sup>2</sup>	
Conductor size: fine-stranded	0.25 - 1.5 mm <sup>2</sup> (with insulated ferrule)	
Conductor size: fine-stranded	0.25 - 2.5 mm <sup>2</sup> (with uninsulated ferrule)	
AWG	24 - 12 (4.1 mm max. outside diameter)	
Strip length	9 - 10 mm / 0.35 - 0.39 in	

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>cu</sub> )
Contact plating	tin-plated

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



For additional derating curves, see page 73.

### Accessories for picoMAX®:

### Page:


Operating tools	64
Direct printing	68
Gripping plates	65
Coding pins	66
Test probe	64



Approvals are available online at: [www.wago.com](http://www.wago.com) \*CSA approval pending  
For more technical information, see Full Line Catalog, Volume 2, Section 11

# Female Connectors picoMAX® 7.5

<b>With gripping plate and sliding connector release</b> <b>Pin spacing: 7.5 mm / 0.295 in</b> 0.2 – 2.5 mm <sup>2</sup>   AWG 24 – 12 630 V/6 kV/2 16 A   300 V/15 A		<b>Mates with:</b>
--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	--	--------------------



L = (pole no. - 1) x pin spacing + 5 mm

Pole No.	Item No.	Pack. Unit
<b>Female connector with gripping plate and sliding connector release, light gray</b>		
2	2092-3102/002-000	100
3	2092-3103/002-000	100
4	2092-3104/002-000	100
5	2092-3105/002-000	100

**Gripping plate dimensions (in mm):**

Pole No.	A	B	C	D	E
2	7	2.75	-	20	-
3	12	4	-	20	-
4 - 5	22	2.75	3.5	25	9

Header with straight solder pins


Header with angled solder pins

Male connector

Panel feedthrough connector

**Outside**

**Inside**



Male header mated to a female connector with gripping plate and sliding connector release.



Push down sliding connector release (gripping plate) to open the locking latch.




Pull out female connector with gripping plate from male header.

7.5

# Female Connectors picoMAX® 7.5

<p>With gripping plate Pin spacing: 7.5 mm / 0.295 in</p>		<p>Mates with:</p>
<p>0.2 - 2.5 mm<sup>2</sup> 630 V/6 kV/2 16 A</p>	<p>AWG 24 - 12 300 V/15 A</p>	






$L = (\text{pole no.} - 1) \times \text{pin spacing} + 5 \text{ mm}$

Pole No.	Item No.	Pack. Unit
<b>Female connector with gripping plate, light gray</b>		
2	2092-3102	100
3	2092-3103	100
4	2092-3104	100
5	2092-3105	100
<b>Product Accessories</b>		<b>Page</b>
Unlocking tool (2092-1630)		64

**Gripping plate dimensions (in mm):**


Pole No.	A	B	C	D	E
2	7	2.75	-	20	-
3	12	4	-	20	-
4 - 5	22	2.75	3.5	25	9



Disconnecting female connector via unlocking tool. Plug unlocking tool into the male header's locking latch.




Insert unlocking tool until it hits backstop. Wedge opens locking latch.



Pull on both unlocking tool and conductors to remove female connector from male header.



# Female Connectors picoMAX® 7.5

<b>Pin spacing: 7.5 mm / 0.295 in</b>		<b>Mates with:</b>
0.2 – 2.5 mm <sup>2</sup> 630 V/6 kV/2 16 A	AWG 24 – 12 300 V/15 A	



L = (pole no. - 1) x pin spacing + 5 mm

Pole No.	Item No.	Pack. Unit
<b>Female connector,</b> light gray		
2	2092-3122	100
3	2092-3123	100
4	2092-3124	100
5	2092-3125	100
<b>Product Accessories</b>		<b>Page</b>
Unlocking tool (2092-1630)		64



Disconnecting female connector via unlocking tool. Plug unlocking tool into the male header's locking latch.



Insert unlocking tool until it hits backstop. Wedge opens locking latch.




Pull on both unlocking tool and conductors to remove female connector from male header.

7.5

# Male Headers with Solder Pins

## picoMAX® 7.5



- Horizontal or vertical plug direction via straight or angled solder pins
- Group female connectors without loss of poles, allowing different functions to be divided within one male header
- Coding pins inserted into the header interface prevent mismatching, allowing subsequent coding in panel feedthrough applications
- Female connector is almost fully shrouded by the male header, providing vibration-resistance up to 20 g\*

### Technical data:

Pin Spacing	7.5 mm 0.295 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	400 V	630 V	1000 V
Rated surge voltage	6 kV	6 kV	6 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA**		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-

### Solder pin data for THT (wave soldering):


Solder pin: length/width	3.6 mm / 1.4 mm Ø
Solder pin: drilled hole diameter	1.6 <sup>+0.1</sup> mm

### Solder pin data for THR\*\*\* (reflow soldering):

Solder pin: length/width	2.4 mm / 1.4 mm Ø
Solder pin: metal-plated hole	1.6 <sup>+0.1</sup> mm Ø

### Material data:

Material group	I
Insulation material/Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated



For additional derating curves, see page 73.

### Accessories for picoMAX®:

Page:

Coding pins	66





The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.



# Male Headers with Solder Pins

## picoMAX® 7.5

<b>With straight solder pins</b> Pin spacing: 7.5 mm / 0.295 in		<b>With angled solder pins</b> Pin spacing: 7.5 mm / 0.295 in		<b>Mates with:</b>
630 V/6 kV/2 16 A	300 V/15 A	630 V/6 kV/2 16 A	300 V/15 A	





$L = (\text{pole no.} - 1) \times \text{pin spacing} + 7.2 \text{ mm}$   
 $A = 3.6 \text{ mm (THT solder pin)}$   
 $A = 2.4 \text{ mm (THR solder pin)}$

Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
Male header with straight solder pins, light gray			Male header with angled solder pins, light gray		
2	2092-3402	100	2	2092-3422	100
3	2092-3403	100	3	2092-3423	100
4	2092-3404	100	4	2092-3424	100
5	2092-3405	100	5	2092-3425	100

Item no. suffix for colored THR version:

○ light gray	...../200-000	<b>Ordering example:</b>
THR male headers with solder pins in tape-and-reel packaging available upon request		THR male header with straight solder pins, 7.5 mm pin spacing, 8-pole, light gray: <b>2092-3408/200-000</b>





7.5




# Male Headers with Solder Pins and Fixing Flanges picoMAX® 7.5

<b>With straight solder pins and fixing flanges</b> <b>Pin spacing: 7.5 mm / 0.295 in</b>		<b>With angled solder pins and fixing flanges</b> <b>Pin spacing: 7.5 mm / 0.295 in</b>		<b>Mates with:</b>
630 V/6 kV/2 16 A	300 V/15 A	630 V/6 kV/2 16 A	300 V/15 A	




$L = (\text{pole no.} - 1) \times \text{pin spacing} + 7.2 \text{ mm}$   
 $L_1 = (\text{pole no.} \times \text{pin spacing}) + 5.5 \text{ mm}$   
 $L_2 = (\text{pole no.} \times \text{pin spacing}) + 4.5 \text{ mm}$   
 $A = 3.6 \text{ mm (THT solder pin)}$   
 $A = 2.4 \text{ mm (THR solder pin)}$




Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
<b>Male header with straight solder pins and fixing flanges, light gray</b>			<b>Male header with angled solder pins and fixing flanges, light gray</b>		
2	2092-3402/005-000	100	2	2092-3422/005-000	100
3	2092-3403/005-000	100	3	2092-3423/005-000	100
4	2092-3404/005-000	100	4	2092-3424/005-000	100
5	2092-3405/005-000	100	5	2092-3425/005-000	100

Item no. suffix for colored THR version:

○ light gray	...../205-000	<b>Ordering example:</b>
THR male headers with solder pins in tape-and-reel packaging available upon request		THR male header with straight solder pins and fixing flanges, 7.5 mm pin spacing, 5-pole, light gray: <b>2092-3405/205-000</b>






7.5

# Male Connectors

## picoMAX® 7.5



- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Easy-to-use design does not require specialty tools
- Testing port parallel to conductor entry – tip contact
- For “wire-to-wire” and “board-to-wire” connections
- Integrated release lever
- Also available with gripping plates

### Technical data:


Pin Spacing	7.5 mm 0.295 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	400 V	630 V	1000 V
Rated surge voltage	6 kV	6 kV	6 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-

### Conductor data:

Connection technology	CAGE CLAMP® S
Conductor size: solid	0.2 – 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.2 – 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.25 – 1.5 mm <sup>2</sup> (with insulated ferrule)
Conductor size: fine-stranded	0.25 – 2.5 mm <sup>2</sup> (with uninsulated ferrule)
AWG	24 – 12 (4.1 mm max. outside diameter)
Strip length	9 – 10 mm / 0.35 – 0.39 in

### Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated



For additional derating curves, see page 73.

### Accessories for picoMAX®:

### Page:




Gripping plates	65
Coding pins	66
Test probe	64

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

# Male Connectors picoMAX® 7.5

CAGE CLAMP® S

Pin spacing: 7.5 mm / 0.295 in		With gripping plate Pin spacing: 7.5 mm / 0.295 in		With snap-in mounting feet Pin spacing: 7.5 mm / 0.295 in	
0.2 - 2.5 mm <sup>2</sup>	AWG 24 - 12	0.2 - 2.5 mm <sup>2</sup>	AWG 24 - 12	0.2 - 2.5 mm <sup>2</sup>	AWG 24 - 12
630 V/6 kV/2 16 A	300 V/15 A	630 V/6 kV/2 16 A	300 V/15 A	630 V/6 kV/2 16 A	300 V/15 A




L = (pole no. - 1) x pin spacing + 7.2 mm  
 Even pole number R = (L - 12 mm) : 2  
 Odd pole number R = (L - 19.5 mm) : 2

7.5

Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
<b>Male connector, light gray</b>			<b>Male connector with gripping plate, light gray</b>			<b>Male connector with snap-in mounting feet, light gray</b>		
for 0.6 - 1.2 mm plate thickness,						for 0.6 - 1.2 mm plate thickness,		
2	2092-3522/002-000	100	2	2092-3502/002-000	100	2	2092-3522/020-000	100
3	2092-3523/002-000	100	3	2092-3503/002-000	100	3	2092-3523/020-000	100
4	2092-3524/002-000	50	4	2092-3504/002-000	50	4	2092-3524/020-000	50
5	2092-3525/002-000	50	5	2092-3505/002-000	50	5	2092-3525/020-000	50
<b>Product Accessories</b>								<b>Page</b>
Mounting adapter for DIN 35 rail, 3 or more poles (209-189)								66

**Gripping plate dimensions (in mm):**


Pole No.	A	B	C	D	E
2	7	3.85	-	20	-
3	12	5.1	-	20	-
4 - 5	22	3.85	3.5	25	9



Standard male connectors can be combined with any female connectors/headers.

# Female Headers with Solder Pins

## picoMAX® 7.5



- Horizontal or vertical PCB mounting via straight or angled solder pins
- Touch-proof PCB outputs
- Easy-to-identify PCB inputs and outputs
- Coding pins available

### Technical data:

Pin Spacing	7.5 mm 0.295 in		
Ratings per	IEC/EN 60664-1		
Overtoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	400 V	630 V	1000 V
Rated surge voltage	6 kV	6 kV	6 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-

### Solder pin data for THT (wave soldering):


Solder pin: length/width	3.6 mm / 0.4 x 1.3 mm
Solder pin: drilled hole diameter	1.5 <sup>+0.1</sup> mm

### Solder pin data for THR\*\* (reflow soldering):

Solder pin: length/width	2.4 mm / 0.4 x 1.3 mm
Solder pin: metal-plated hole	1.5 <sup>+0.1</sup> mm Ø

### Material data:

Material group	I
Insulation material/Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Contact material	Copper alloy
Contact plating	tin-plated



For additional derating curves, see page 73.

### Accessories for picoMAX®:

### Page:



Coding pins	66

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984. When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

# Female Headers with Solder Pins


## picoMAX® 7.5

With straight solder pins Pin spacing: 7.5 mm / 0.295 in		With angled solder pins Pin spacing: 7.5 mm / 0.295 in		Mates with:
630 V/6 kV/2 16 A	300 V/15 A	630 V/6 kV/2 16 A	300 V/15 A	



L = (pole no. - 1) x pin spacing + 5 mm  
 A = 3.6 mm (THT solder pin)  
 A = 2.4 mm (THR solder pin)

Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
Female header with straight solder pins, light gray			Female header with angled solder pins, light gray		
2	2092-3302	100	2	2092-3322	100
3	2092-3303	100	3	2092-3323	100
4	2092-3304	100	4	2092-3324	100
5	2092-3305	100	5	2092-3325	100



### Item no. suffix for colored THR version:

○ light gray	...../200-000	<b>Ordering example:</b>
THR female headers with solder pins in tape-and-reel packaging available upon request		THR female header with straight solder pins, 5 mm pin spacing, 5-pole, light gray: <b>2092-3305/200-000</b>

7.5



**A RADICALLY SIMPLIFIED CONNECTOR CAN'T POSSIBLY HAVE WHAT IT TAKES.**

**YES IT CAN.**

**picoMAX<sup>®</sup> eCOM – It doesn't get any easier!**

picoMAX<sup>®</sup> eCOM is the easiest way to make PCBs pluggable.

If you don't need all picoMAX<sup>®</sup> functionalities, opt for an **even more efficient and compact version** without pin housing – **picoMAX<sup>®</sup> eCOM**.

With 3.5 mm (0.138 in), 5.0 mm (0.197 in) and 7.5 mm (0.295 in) pin spacing, this system of **pin strip pluggable terminal blocks for direct soldering to PCB** is the ideal solution for **cost-efficient PCB applications**. The connectors are delivered with solder pins in place, so they can be mounted and soldered to the PCB just as you would for a conventional PCB component. picoMAX<sup>®</sup> eCOM is suitable for all conductor types via CAGE CLAMP<sup>®</sup> S universal connection. Furthermore, solid and ferruled conductors are connected by simply pushing them into unit.


During maintenance, **picoMAX<sup>®</sup> eCOM can be removed from the circuit board like a pluggable connector**. This allows PCB or components to be replaced without costly rewiring. Connectors of different lengths can be arranged side by side without loss of poles, **maximizing space savings** on the PCB! The pluggable PCB terminal blocks are also available as versions for THR soldering!

These features make picoMAX<sup>®</sup> eCOM **extremely efficient, pluggable PCB terminal blocks**. picoMAX<sup>®</sup> eCOM is available as straight and angled PCB terminal block for conductors 0.2–1.5 mm<sup>2</sup> (AWG 24–14) with 3.5 mm (0.138 in), as well as 0.2–2.5 mm<sup>2</sup> (24–12) with 5.0 mm (0.197 in) and 7.5 mm (0.295 in) pin spacing.

**picoMAX<sup>®</sup>: Highly efficient system.**



## Pin strip pluggable terminal blocks for direct soldering to PCB



Actual size:  
3.5 mm pin spacing

COMPACT

VIBRATION-PROOF


INTUITIVE

UNIVERSAL

EFFICIENT


# PCB Terminal Blocks that Double as Pluggable Connectors

1. Place and solder the pluggable terminal blocks as marked on the PCB




*picoMAX® eCOM* pin strip pluggable terminal blocks are delivered with solder pins so they can be directly soldered to a PCB and then wired just as traditional PCB terminal blocks are. *CAGE CLAMP®S* allows stranded and fine-stranded conductors to be terminated via push-buttons. Solid and ferruled conductors are terminated by simply pushing them into the wiring port. For ease of maintenance, the pluggable terminal blocks can be removed without altering the wiring and then plugged onto the spare PCB.

2. Wired terminal blocks




3. During maintenance




# Handling *picoMAX*<sup>®</sup> eCOM

Pin Spacing: 3.5 mm/0.138 in, 5.0 mm/0.197 in and 7.5 mm/0.295 in



Testing with 1 mm Ø Test probe, tip contact.



Terminating fine-stranded conductors and removing all conductor types via push-buttons.




Terminating solid and ferruled conductors via push-in termination.



Horizontal or vertical plug direction.



THR version with shorter solder pins.



Pole marking via direct printing perpendicular to conductor entry.




Pole marking via direct printing parallel to conductor entry.

**Notice:**

*picoMAX*<sup>®</sup> eCOM shall only be used with factory-installed solder pins!

# picoMAX® eCOM 3.5 – Pin Strip Pluggable Terminal Block for Direct Soldering to PCB



- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Easy-to-use design does not require specialty tools
- Ability to wire while mated or unmated
- Integrated test ports for testing parallel to conductor entry
- Factory-installed, straight or angled solder pins allow horizontal or vertical plug direction to the PCB

## Technical data:

Pin Spacing	3.5 mm 0.138 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	160 V	160 V	320 V
Rated surge voltage	2.5 kV	2.5 kV	2.5 kV
Nominal current	10 A	10 A	10 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	10	-	10
Nominal current CSA	-	-	-

## Conductor data:

Connection technology	CAGE CLAMP® S
Conductor size: solid	0.2 – 1.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.2 – 1.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.25 – 0.75 mm <sup>2</sup> (with insulated ferrule)
Conductor size: fine-stranded	0.25 – 1.5 mm <sup>2</sup> (with uninsulated ferrule)
AWG	24 – 14 (2.8 mm max. outside diameter)
Strip length	8 – 9 mm / 0.31 – 0.35 in

## Solder pin data for THT (wave soldering):

Solder pin: length/width	3.6 mm / 1.0 mm Ø
Solder pin: drilled hole diameter	1.2 <sup>+0.1</sup> mm

## Solder pin data for THR\*\* (reflow soldering):

Solder pin: length/width	2.4 mm / 1.0 mm Ø
Solder pin: metal-plated hole	1.2 <sup>+0.1</sup> mm Ø


## Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	65°C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated

The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984.

When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

Approvals are available online at: [www.wago.com](http://www.wago.com) \*CSA approval pending \*\* For THR soldering, see page 69



For additional derating curves, see page 74.

## Accessories for picoMAX®:

## Page:



Operating tools	64
Test probe	64
Gripping plates	65
Direct printing	68



# picoMAX® eCOM 3.5 – Pin Strip Pluggable Terminal Block for Direct Soldering to PCB

CAGE CLAMP® S

With straight solder pins Pin spacing: 3.5 mm / 0.138 in		With angled solder pins Pin spacing: 3.5 mm / 0.138 in	
0.2 - 1.5 mm <sup>2</sup>	AWG 24 - 14	0.2 - 1.5 mm <sup>2</sup>	AWG 24 - 14
160 V/2.5 kV/2 10 A	300 V/10 A	160 V/2.5 kV/2 10 A	300 V/10 A




L = pole no. x pin spacing  
A = 3.6 mm (THT solder pin)  
A = 2.4 mm (THR solder pin)

Pole No.	Item No.	Item No.	Pack. Unit	Pole No.	Item No.	Item No.	Pack. Unit	Gripping plate dimensions (in mm):					
								Pole No.	A	B	C	D	E
<b>eCOM pluggable female header with straight solder pins, light gray</b>				<b>eCOM pluggable female header with angled solder pins, light gray</b>									
	Gripping plate:			Gripping plate:									
	without	with		without	with								
2	2091-1172	2091-1152		2	2091-1372	2091-1352		2	-	17	-		
3	2091-1173	2091-1153		3	2091-1373	2091-1353		6	2.25	-	17	-	
4	2091-1174	2091-1154		4	2091-1374	2091-1354		6	2.25	-	17	-	
5	2091-1175	2091-1155		5	2091-1375	2091-1355		13	2.25	3	20	5	
6	2091-1176	2091-1156		6	2091-1376	2091-1356		13	2.25	3	20	5	
8	2091-1178	2091-1158		8	2091-1378	2091-1358		13	5.75	3	20	5	
10	2091-1180	2091-1160		10	2091-1380	2091-1360		27	2.25	4.2	25	8	
12	2091-1182	2091-1162		12	2091-1382	2091-1362		27	5.75	4.2	25	8	

Item no. suffix for colored THR version:


○ light gray	...../200-000	<b>Ordering example:</b>
		eCOM THR pluggable female header with straight solder pins,
		3.5 mm pin spacing, 8-pole, light gray
		<b>2091-1178/200-000</b>
		THR version only for female headers <u>without</u> gripping plate



3.5

For other lengths, please contact factory.

# picoMAX® eCOM 5.0 – Pin Strip Pluggable Terminal Block for Direct Soldering to PCB



- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Easy-to-use design does not require specialty tools
- Ability to wire while mated or unmated
- Integrated test ports for testing parallel to conductor entry
- Factory-installed, straight or angled solder pins allow horizontal or vertical plug direction to the PCB

## Technical data:

Pin Spacing	5 mm 0.197 in		
Ratings per	IEC/EN 60664-1		
Overtoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	250 V	320 V	630 V
Rated surge voltage	4 kV	4 kV	4 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-

## Conductor data:

Connection technology	CAGE CLAMP® S
Conductor size: solid	0.2 – 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.2 – 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.25 – 1.5 mm <sup>2</sup> (with insulated ferrule)
Conductor size: fine-stranded	0.25 – 2.5 mm <sup>2</sup> (with uninsulated ferrule)
AWG	24 – 12 (4.1 mm max. outside diameter)
Strip length	9 – 10 mm / 0.35 – 0.39 in

## Solder pin data for THT (wave soldering):

Solder pin: length/width	3.6 mm / 1.4 mm Ø
Solder pin: drilled hole diameter	1.6 <sup>+0.1</sup> mm

## Solder pin data for THR\*\* (reflow soldering):

Solder pin: length/width	2.4 mm / 1.4 mm Ø
Solder pin: metal-plated hole	1.6 <sup>+0.1</sup> mm Ø

## Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated


The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984.

When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

Approvals are available online at: [www.wago.com](http://www.wago.com) \*CSA approval pending \*\* For THR soldering, see page 69

## Derating Curve

2092-1172 eCOM pluggable female header,  
Pin spacing: 5 mm / Conductor size: 2.5 mm<sup>2</sup> "f-st"  
Based on: EN 60512-5-2 / Reduction factor: 0.8



For additional derating curves, see page 74.

## Accessories for picoMAX®:

## Page:




Operating tools	64
Test probe	64
Gripping plates	65
Direct printing	68



# picoMAX® eCOM 5.0 – Pin Strip Pluggable Terminal Block for Direct Soldering to PCB

CAGE CLAMP® 

With straight solder pins Pin spacing: 5 mm / 0.197 in		With angled solder pins Pin spacing: 5 mm / 0.197 in	
0.2 - 2.5 mm <sup>2</sup> 320 V/4 kV/2 16 A	AWG 24 - 12 300 V/15 A	0.2 - 2.5 mm <sup>2</sup> 320 V/4 kV/2 16 A	AWG 24 - 12 300 V/15 A




L = pole no. x pin spacing  
A = 3.6 mm (THT solder pin)  
A = 2.4 mm (THR solder pin)

Pole No.	Item No.	Item No.	Pack. Unit	Pole No.	Item No.	Item No.	Pack. Unit	Gripping plate dimensions (in mm):						
								Pole No.	A	B	C	D	E	
eCOM pluggable female header with straight solder pins, light gray				eCOM pluggable female header with angled solder pins, light gray										
Gripping plate: without      with				Gripping plate: without      with										
2	2092-1172	2092-1152		2	2092-1372	2092-1352		2	7	1.5	-	20	-	
3	2092-1173	2092-1153		3	2092-1373	2092-1353		3	12	1.5	-	20	-	
4	2092-1174	2092-1154		4	2092-1374	2092-1354		4	12	1.5	-	20	-	
5	2092-1175	2092-1155		5	2092-1375	2092-1355		5	22	1.5	3.5	25	9	
6	2092-1176	2092-1156		6	2092-1376	2092-1356		6	22	1.5	3.5	25	9	
8	2092-1178	2092-1158		8	2092-1378	2092-1358		8	22	6.5	3.5	25	9	
10	2092-1180	2092-1160		10	2092-1380	2092-1360		10	42	1.5	5	35	19	
12	2092-1182	2092-1162		12	2092-1382	2092-1362		12	42	6.5	5	35	19	

Item no. suffix for colored THR version:

<input type="radio"/> light gray	...../200-000	<b>Ordering example:</b> eCOM THR pluggable female header with straight solder pins, 5 mm pin spacing, 8-pole, light gray <b>2092-1178/200-000</b>
THR version only for female headers without gripping plate		




5.0

For other lengths, please contact factory.



# picoMAX® eCOM 7.5 – Pin Strip Pluggable Terminal Block for Direct Soldering to PCB



- Universal connection for all conductor types
- Simple, push-in termination of solid and ferruled conductors
- Easy-to-use design does not require specialty tools
- Ability to wire while mated or unmated
- Integrated test ports for testing parallel to conductor entry
- Factory-installed, straight or angled solder pins allow horizontal or vertical plug direction to the PCB

## Technical data:

Pin Spacing	7.5 mm 0.295 in		
Ratings per	IEC/EN 60664-1		
Overvoltage category	III	III	II
Pollution degree	3	2	2
Rated voltage	400 V	630 V	1000 V
Rated surge voltage	6 kV	6 kV	6 kV
Nominal current	16 A	16 A	16 A
Temperature range	-60°C/+100°C		
Approvals per	UL/CSA*		
Use group UL 1059	B	C	D
Rated voltage	300	-	300
Nominal current UL	15	-	15
Nominal current CSA	-	-	-

## Conductor data:

Connection technology	CAGE CLAMP® S
Conductor size: solid	0.2 – 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.2 – 2.5 mm <sup>2</sup>
Conductor size: fine-stranded	0.25 – 1.5 mm <sup>2</sup> (with insulated ferrule)
Conductor size: fine-stranded	0.25 – 2.5 mm <sup>2</sup> (with uninsulated ferrule)
AWG	24 – 12 (4.1 mm max. outside diameter)
Strip length	9 – 10 mm / 0.35 – 0.39 in

## Solder pin data for THT (wave soldering):

Solder pin: length/width	3.6 mm / 1.4 mm Ø
Solder pin: drilled hole diameter	1.6 <sup>+0.1</sup> mm

## Solder pin data for THR\*\* (reflow soldering):

Solder pin: length/width	2.4 mm / 1.4 mm Ø
Solder pin: metal-plated hole	1.6 <sup>+0.1</sup> mm Ø

## Material data:

Material group	I
Insulation material	Glass-fiber-reinforced polyphthalamide (PPA-GF)
Flammability rating per UL 94	V0
Material temperature rating acc. to UL1059	125°C
Clamping spring material	Chrome nickel spring steel (CrNi)
Contact material	Electrolytic copper (E <sub>Cu</sub> )
Contact plating	tin-plated


The **picoMAX® pluggable connection system** includes connectors without breaking capacity in accordance with DIN EN 61984.

When used as intended, these connectors shall not be connected/disconnected when live or under load. The circuit design should ensure header pins, which can be touched, are not live when unmated.

Approvals are available online at: [www.wago.com](http://www.wago.com) \*CSA approval pending \*\* For THR soldering, see page 69

## Derating Curve

2092-3174 eCOM pluggable female header,  
Pin spacing: 7.5 mm / Conductor size: 2.5 mm<sup>2</sup> "f-st"  
Based on: EN 60512-5-2 / Reduction factor: 0.8



For additional derating curves, see page 74.

## Accessories for picoMAX®:



## Page:

Operating tools	64
Test probe	64
Gripping plates	65
Direct printing	68

# picoMAX® eCOM 7.5 – Pin Strip Pluggable Terminal Block for Direct Soldering to PCB

CAGE CLAMP® 

With straight solder pins Pin spacing: 7.5 mm / 0.295 in		With angled solder pins Pin spacing: 7.5 mm / 0.295 in	
0.2 - 2.5 mm <sup>2</sup> 630 V/6 kV/2 16 A	AWG 24 - 12 300 V/15 A	0.2 - 2.5 mm <sup>2</sup> 630 V/6 kV/2 16 A	AWG 24 - 12 300 V/15 A




L = (pole no. - 1) x pin spacing + 5 mm  
A = 3.6 mm (THT solder pin)  
A = 2.4 mm (THR solder pin)

Pole No.	Item No.	Item No.	Pack. Unit	Pole No.	Item No.	Item No.	Pack. Unit	Gripping plate dimensions (in mm):					
								Pole No.	A	B	C	D	E
eCOM pluggable female header with straight solder pins, light gray				eCOM pluggable female header with angled solder pins, light gray									
Gripping plate: without      with				Gripping plate: without      with									
2	2092-3172	2092-3152		2	2092-3372	2092-3352		2	7	2.75	-	20	-
3	2092-3173	2092-3153		3	2092-3373	2092-3353		3	12	4	-	20	-
4	2092-3174	2092-3154		4	2092-3374	2092-3354		4 - 5	22	2.75	3.5	25	9
5	2092-3175	2092-3155		5	2092-3375	2092-3355							

Item no. suffix for colored THR version:

<input type="radio"/> light gray	...../200-000	<b>Ordering example:</b> eCOM THR pluggable female header with straight solder pins, 7.5 mm pin spacing, 5-pole, light gray <b>2092-3175/200-000</b>
THR version only for female headers <u>without</u> gripping plate		



For other lengths, please contact factory.


7.5

# Accessories for picoMAX®


<b>Operating tool</b> with partially insulated shaft Type 1	<b>Unlocking tool</b> for female connectors without gripping plate or sliding connector release	<b>Test probe</b>
-------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------	-------------------



Item No.	Pack. Unit	Item No.	Pack. Unit	Item No.	Pack. Unit
<b>Operating tool</b> , with partially insulated shaft, type 1, (2.5 x 0.4) mm blade		<b>Unlocking tool</b> , orange		<b>Test probe</b> , 1 mm Ø, with solder connection for test cable	
<b>210-719</b>	1	<b>2092-1630</b>	100 (4 x 25)	<b>735-500</b>	1




Inserting/removing conductor.




Disconnecting female connector via unlocking tool. Plug unlocking tool into the male header's locking latch.



Testing with 1 mm Ø test probe, tip contact.



Insert unlocking tool until it hits backstop. Wedge opens locking latch.



Pull on both unlocking tool and conductors to remove female connector from male header.

# Accessories for *picoMAX*<sup>®</sup>

<b>Gripping plates,</b> for field assembly	<b>Gripping plates with sliding connector release,</b> for field assembly	
-----------------------------------------------	------------------------------------------------------------------------------	--



Pole No.	Item No.	Pack. Unit	Pole No.	Item No.	Pack. Unit
<b>Gripping plate,</b> light gray			<b>Gripping plate with sliding connector release,</b> light gray		
Pin spacing: 3.5 mm			Pin spacing: 3.5 mm		
2	<b>2091-1600</b>	100 (4 x 25)	2	<b>2091-1600/002-000</b>	100 (4 x 25)
3- 4	<b>2091-1601</b>	100 (4 x 25)	3- 4	<b>2091-1601/002-000</b>	100 (4 x 25)
5- 8	<b>2091-1602</b>	100 (4 x 25)	5- 8	<b>2091-1602/002-000</b>	100 (4 x 25)
9-12	<b>2091-1603</b>	100 (4 x 25)	9-12	<b>2091-1603/002-000</b>	100 (4 x 25)
Pin spacing: 5 mm			Pin spacing: 5 mm		
2	<b>2092-1600</b>	100 (4 x 25)	2	<b>2092-1600/002-000</b>	100 (4 x 25)
3- 4	<b>2092-1601</b>	100 (4 x 25)	3- 4	<b>2092-1601/002-000</b>	100 (4 x 25)
5- 8	<b>2092-1602</b>	100 (4 x 25)	5- 8	<b>2092-1602/002-000</b>	100 (4 x 25)
9-12	<b>2092-1603</b>	100 (4 x 25)	9-12	<b>2092-1603/002-000</b>	100 (4 x 25)
Pin spacing: 7.5 mm			Pin spacing: 7.5 mm		
2	<b>2092-3600</b>	100 (4 x 25)	2	<b>2092-3600/002-000</b>	100 (4 x 25)
3- 4	<b>2092-3601</b>	100 (4 x 25)	3- 4	<b>2092-3601/002-000</b>	100 (4 x 25)
5	<b>2092-3602</b>	100 (4 x 25)	5	<b>2092-3602/002-000</b>	100 (4 x 25)
6	<b>2092-3603</b>	100 (4 x 25)	6	<b>2092-3603/002-000</b>	100 (4 x 25)



Gripping plates are suitable for factory and in-the-field assembly.

# Accessories for *picoMAX*<sup>®</sup>

<p><b>Coding key carrier</b></p> <p>with 2 coding keys for each male header and female connector</p>	<p><b>Mounting adapter for DIN 35 rail</b></p> <p>for male connectors with snap-in mounting feet</p>	
------------------------------------------------------------------------------------------------------	------------------------------------------------------------------------------------------------------	--



Item No.	Pack. Unit	Item No.	Pack. Unit
<b>Coding key carrier</b> , with 2 coding keys for each male header and female connector, orange		<b>Mounting adapter</b> , for male connectors with snap-in mounting feet, gray	
Pin spacing: 3.5 mm			
<b>2091-1610</b>	100 (4 x 25)	<b>209-189</b>	25
Pin spacing: 5 mm and 7.5 mm			
<b>2092-1610</b>	100 (4 x 25)		



Coding a male header (via coding key carrier and two keys for male header, see symbol).



Male connector with snap-in mounting feet and 209-189 mounting adapter on DIN 35 rail.



Coding a female connector (via coding key carrier and two keys for female connector, see symbol).



# Ferrules

<b>Uninsulated ferrules</b>  Electrolytic copper, electro tin-plated, acc. to DIN 46288, part 1/08.92	<b>Insulated ferrules</b>  Electrolytic copper, electro tin-plated, acc. to DIN 46288, part 4/09.09	<b>"Variocrimp 4" crimping tool</b>  0.25 – 4 mm <sup>2</sup> / AWG 22 – 12
----------------------------------------------------------------------------------------------------------------	--------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------



Item No.	Pack. Unit	Item No.	Pack. Unit	Item No.	Pack. Unit
Uninsulated ferrule for <b>0.25 mm<sup>2</sup>/AWG 24</b> <b>L: 5 mm</b> , D: 1.7 mm, D <sub>2</sub> : 0.75 mm, 5 mm strip length <b>216-151</b>	1000	Insulated ferrule for <b>0.25 mm<sup>2</sup>/AWG 24</b> , 7.5 mm strip length, L: 10 mm, <b>L<sub>1</sub>: 6 mm</b> , D: 2.3 mm, D <sub>1</sub> : 1.8 mm, D <sub>2</sub> : 0.85 mm yellow <b>216-321</b>	1000	<b>"Variocrimp 4" crimping tool</b> , for insulated and uninsulated ferrules, crimping range of 0.25 – 4 mm <sup>2</sup>  <b>206-204</b>	1
<b>L: 7 mm</b> , D: 1.7 mm, D <sub>2</sub> : 0.75 mm, 7 mm strip length <b>216-131</b>	1000	L: 12 mm, <b>L<sub>1</sub>: 8 mm</b> , 9.5 mm strip length yellow <b>216-301</b>	1000		
Uninsulated ferrule for <b>0.34 mm<sup>2</sup>/AWG 24</b> <b>L: 5 mm</b> , D: 1.8 mm, D <sub>2</sub> : 0.75 mm, 5 mm strip length <b>216-152</b>	1000	Insulated ferrule for <b>0.34 mm<sup>2</sup>/AWG 24</b> , 7.5 mm strip length, L: 10 mm, <b>L<sub>1</sub>: 6 mm</b> , D: 2.5 mm, D <sub>1</sub> : 2 mm, D <sub>2</sub> : 0.85 mm green <b>216-322</b>	1000		
<b>L: 7 mm</b> , D: 1.8 mm, D <sub>2</sub> : 0.85 mm, 7 mm strip length <b>216-132</b>	1000	L: 12 mm, <b>L<sub>1</sub>: 8 mm</b> , 9.5 mm strip length green <b>216-302</b>	1000		
Uninsulated ferrule for <b>0.5 mm<sup>2</sup>/AWG 22</b> <b>L: 6 mm</b> , D: 2.1 mm, D <sub>2</sub> : 1 mm, 6 mm strip length <b>216-121</b>	1000	Insulated ferrule for <b>0.5 mm<sup>2</sup>/AWG 22</b> , 7.5 mm strip length, L: 12 mm, <b>L<sub>1</sub>: 6 mm</b> , D: 3.1 mm, D <sub>1</sub> : 2.6 mm, D <sub>2</sub> : 1 mm white <b>216-221</b>	1000		
<b>L: 8 mm</b> , D: 2.1 mm, D <sub>2</sub> : 1 mm, 8 mm strip length <b>216-101</b>	1000	L: 14 mm, <b>L<sub>1</sub>: 8 mm</b> , 9.5 mm strip length white <b>216-201</b>	1000		
Uninsulated ferrule for <b>0.75 mm<sup>2</sup>/AWG 20</b> <b>L: 6 mm</b> , D: 2.3 mm, D <sub>2</sub> : 1.2 mm, 6 mm strip length <b>216-122</b>	1000	Insulated ferrule for <b>0.75 mm<sup>2</sup>/AWG 20</b> , 8 mm strip length, L: 12 mm, <b>L<sub>1</sub>: 6 mm</b> , D: 3.3 mm, D <sub>1</sub> : 2.8 mm, D <sub>2</sub> : 1.2 mm gray <b>216-222</b>	1000		
<b>L: 8 mm</b> , D: 2.3 mm, D <sub>2</sub> : 1.2 mm, 8 mm strip length <b>216-102</b>	1000	L: 14 mm, <b>L<sub>1</sub>: 8 mm</b> , 10 mm strip length gray <b>216-202</b>	1000		
Uninsulated ferrule for <b>1 mm<sup>2</sup>/AWG 18</b> <b>L: 6 mm</b> , D: 2.5 mm, D <sub>2</sub> : 1.4 mm, 6 mm strip length <b>216-123</b>	1000	Insulated ferrule for <b>1 mm<sup>2</sup>/AWG 18</b> , 8 mm strip length, L: 12 mm, <b>L<sub>1</sub>: 6 mm</b> , D: 3.5 mm, D <sub>1</sub> : 3 mm, D <sub>2</sub> : 1.4 mm red <b>216-223</b>	1000		
<b>L: 8 mm</b> , D: 2.5 mm, D <sub>2</sub> : 1.4 mm, 8 mm strip length <b>216-103</b>	1000	L: 14 mm, <b>L<sub>1</sub>: 8 mm</b> , 10 mm strip length red <b>216-203</b>	1000		
Uninsulated ferrule for <b>1.5 mm<sup>2</sup>/AWG 16</b> <b>L: 6 mm</b> , D: 2.8 mm, D <sub>2</sub> : 1.7 mm, 6 mm strip length <b>216-124</b>	1000	Insulated ferrule for <b>1.5 mm<sup>2</sup>/AWG 16</b> , 8 mm strip length, L: 12 mm, <b>L<sub>1</sub>: 6 mm</b> , D: 4 mm, D <sub>1</sub> : 3.5 mm, D <sub>2</sub> : 1.7 mm black <b>216-224</b>	1000		
<b>L: 8 mm</b> , D: 2.8 mm, D <sub>2</sub> : 1.7 mm, 8 mm strip length <b>216-104</b>	1000	L: 14 mm, <b>L<sub>1</sub>: 8 mm</b> , 10 mm strip length black <b>216-204</b>	1000		
Uninsulated ferrule for <b>2.5 mm<sup>2</sup>/AWG 14</b> <b>L: 8 mm</b> , D: 3.4 mm, D <sub>2</sub> : 2.2 mm, 8 mm strip length <b>216-105</b>	1000				
<b>L: 10 mm</b> , D: 3.4 mm, D <sub>2</sub> : 2.2 mm, 10 mm strip length <b>216-106</b>	1000				

- Application notes:**
- With "Variocrimp 4," the built-in crimping pressure control automatically adjusts force to the conductor cross section used. With "Variocrimp 16," it is necessary to select the wire gauge on the tool before crimping.
  - Only one crimping station is needed to handle the specified conductor size range.
  - Uniform, compact crimping on all four sides for high conductor retention.
  - No need to center the conductor into the ferrule.
  - Conductor and ferrule insertion possible from both sides (for left- and right-handers).
  - Built-in ratchet mechanism ensures gastight crimp connection.
  - Crimping tools open automatically after crimping operation is complete.
  - Ergonomically designed handles.




A perfect gastight crimp, both electrically and mechanically reliable.



# Accessories for *picoMAX*<sup>®</sup> Printing for 2091 and 2092 Series

<p>Direct printing on female connectors</p> <p><b>"Wire-to-board"</b></p> <p>1 – Pole number</p>	<p>Direct printing on female connectors</p> <p><b>"Wire-to-wire"</b></p> <p>1 – Pole number</p>	<p>Direct printing on male connectors</p> <p><b>"Wire-to-board" and "wire-to-wire"</b></p> <p>1 – Pole number</p>
--------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------





<p>Printing Parallel to Conductor Entry Item No. Suffix: /...-1000</p> <p>Ordering examples:</p> <p><b>Female connector,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1126/0000-1000</p> <p><b>Female connector with gripping plate,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1106/0000-1000</p> <p><b>Female connector with gripping plate and sliding connector release,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1106/0002-1000</p>	<p>Printing Parallel to Conductor Entry Item No. Suffix: /...-3000</p> <p>Ordering examples:</p> <p><b>Female connector,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1126/0000-3000</p> <p><b>Female connector with gripping plate,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1106/0000-3000</p> <p><b>Female connector with gripping plate and sliding connector release,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1106/0002-3000</p>	<p>Printing Parallel to Conductor Entry Item No. Suffix: /...-3000</p> <p>Ordering examples:</p> <p><b>Male connector,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1526/0002-3000</p> <p><b>Male connector with gripping plate,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1506/0002-3000</p>
---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

<p>Printing Perpendicular to Conductor Entry Item no. suffix: /...-5000</p> <p>Ordering examples:</p> <p><b>Female connector,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1376/0000-5000</p> <p><b>Female connector with gripping plate,</b> 3.5 mm pin spacing, 6-pole, light gray 2091-1356/0000-5000</p>
-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------






# THR (Through-Hole Reflow) Soldering Process




By using high-temperature-resistant plastic and a streamlined pin design, the WAGO **Through-Hole Reflow** headers and PCB terminal blocks meet requirements for SMT process capability while maintaining the necessary stability. Male headers and THR PCB terminal blocks are simply pushed into the solder paste-filled PCB holes and then soldered along with the SMT components via reflow soldering. The previous wave soldering process is no longer necessary. The result is a perfect connection – both mechanically and electrically.


WAGO **THR** male headers in tape-and-reel packaging acc. to IEC 60286-3 are available upon request.




Metal-plated PCB bore hole




SMD positioning pattern




Application of solder paste



Component assembly, automatic/by hand




Reflow soldering process



THR soldering joint

Series	$d_i$ (mm)	$d_A$ (mm)	H(mm)	$d_s$ (mm)	$D_s$ ( $\mu$ m)	d(mm)	L(mm)
2091	$1.2^{+0.1}$	1.9	< 2	1.8	150	1.0 $\emptyset$	2.4
2091	$1.2^{+0.1}$	1.9	< 2	1.8	150	0.4 x 0.5	2.4
2092	$1.6^{+0.1}$	2.3	< 2	2.2	150	1.4 $\emptyset$	2.4
2092	$1.5^{+0.1}$	2.2	< 2	2.1	150	0.4 x 1.3	2.4



- $d_i$ : Inner diameter of metal-plated PCB bore hole
- $d_A$ : Outer diameter of metal-plated PCB hole\*
- H: PCB thickness
- $d_s$ : Pattern hole diameter
- $D_s$ : Pattern thickness
- d: Pin cross section
- L: Pin length

\* When laying out the metal-plated bore holes, the clearance and creepage distance requirements – as specified in the equipment standards – must be considered.


WAGO recommends a temperature profile for processing THR components (see "Technical Section").

Depending on reflow soldering temperatures and times, color deviations may occur for light gray connectors. These deviations will have no impact on functionality.

## Technical Section

### • Contact Resistance

Typical contact resistance values for various conductor sizes for *picoMAX*® 2091 and 2092 Series “wire-to-board” and “wire-to-wire” pluggable connections (see table below).



Conductor Size in mm <sup>2</sup>		“Wire-to-Board”		“Wire-to-Wire”	
		2091 Series	2092 Series	2091 Series	2092 Series
0.25	fine-stranded	1.43 mΩ	1.83 mΩ	2.58 mΩ	5.71 mΩ
0.5	fine-stranded	1.09 mΩ	1.15 mΩ	1.64 mΩ	2.28 mΩ
1.0	fine-stranded	0.99 mΩ	0.91 mΩ	1.43 mΩ	1.41 mΩ
1.5	fine-stranded	0.72 mΩ	0.71 mΩ	1.02 mΩ	1.20 mΩ
2.5	fine-stranded	-	0.60 mΩ	-	1.09 mΩ
0.25	fine-stranded, with ferrule	0.79 mΩ	0.78 mΩ	1.44 mΩ	1.40 mΩ
0.5	fine-stranded, with ferrule	0.69 mΩ	0.58 mΩ	1.10 mΩ	1.06 mΩ
1.0	fine-stranded, with ferrule	0.52 mΩ	0.46 mΩ	0.83 mΩ	0.82 mΩ
1.5	fine-stranded, with ferrule	0.51 mΩ	0.38 mΩ	0.82 mΩ	0.69 mΩ
2.5	fine-stranded, with ferrule	-	0.38 mΩ	-	0.61 mΩ

### • Connecting Ferrules for 2091 and 2092 Series

Conductor Size in mm <sup>2</sup>		Ferrule Item No.	
		2091 Series	2092 Series
0.25	fine-stranded, with insulated ferrule	216-301	216-301
0.34	fine-stranded, with insulated ferrule	216-302	216-302
0.5	fine-stranded, with insulated ferrule	216-201	216-201
0.75	fine-stranded, with insulated ferrule	216-202	216-202
1.0	fine-stranded, with insulated ferrule	-	216-203
1.5	fine-stranded, with insulated ferrule	-	216-204
0.25	fine-stranded, with ferrule	216-131	216-131
0.34	fine-stranded, with ferrule	216-132	216-132
0.5	fine-stranded, with ferrule	216-101	216-101, 216-141
0.75	fine-stranded, with ferrule	216-102	216-102, 216-142
1.0	fine-stranded, with ferrule	216-103	216-103, 216-143
1.5	fine-stranded, with ferrule	216-104	216-104, 216-144
2.5	fine-stranded, with ferrule	-	216-106

- Current-Carrying Capacity Curve (Derating Curve) to EN 60512-5-2 / Reduction Factor: 0.8


**picoMAX®, 2091 Series, 3.5 mm pin spacing**

**“Wire-to-board” connection**




Example: female connector and male header

**1.0 mm<sup>2</sup> test conductor, fine-stranded**



2-, 6-, 12-pole — Conductor rated current

**1.5 mm<sup>2</sup> test conductor, fine-stranded**




**“Board-to-wire” connection**




Example: Female header and male connector

**1.0 mm<sup>2</sup> test conductor, fine-stranded**




6-pole — Conductor rated current

**1.5 mm<sup>2</sup> test conductor, fine-stranded**




**“Wire-to-wire” connection**




Example: female and male connector

**1.0 mm<sup>2</sup> test conductor, fine-stranded**



2-, 6-pole — Conductor rated current

**1.5 mm<sup>2</sup> test conductor, fine-stranded**



# Technical Section

• Current-Carrying Capacity Curve (Derating Curve) to EN 60512-5-2 / Reduction Factor: 0.8


## picoMAX®, 2092 Series, 5.0 mm pin spacing

### “Wire-to-board” connection




Example: female connector and male header

#### 1.5 mm<sup>2</sup> test conductor, fine-stranded



2-, 6-, 12-pole — Conductor rated current

#### 2.5 mm<sup>2</sup> test conductor, fine-stranded




2-, 6-, 12-pole — Conductor rated current

### “Board-to-wire” connection




Example: Female header and male connector

#### 1.5 mm<sup>2</sup> test conductor, fine-stranded




2-, 6-pole — Conductor rated current

#### 2.5 mm<sup>2</sup> test conductor, fine-stranded




2-, 6-pole — Conductor rated current

### “Wire-to-wire” connection




Example: female and male connector

#### 1.5 mm<sup>2</sup> test conductor, fine-stranded



6-pole — Conductor rated current

#### 2.5 mm<sup>2</sup> test conductor, fine-stranded



6-pole — Conductor rated current

- Current-Carrying Capacity Curve (Derating Curve) to EN 60512-5-2 / Reduction Factor: 0.8


**picoMAX<sup>®</sup>, 2092 Series, 7.5 mm pin spacing**

**“Wire-to-board” connection**




Example: female connector and male header

**1.5 mm<sup>2</sup> test conductor, fine-stranded**



4-pole — Conductor rated current

**2.5 mm<sup>2</sup> test conductor, fine-stranded**




4-pole — Conductor rated current

**“Board-to-wire” connection**




Example: Female header and male connector

**1.5 mm<sup>2</sup> test conductor, fine-stranded**




4-pole — Conductor rated current

**2.5 mm<sup>2</sup> test conductor, fine-stranded**




4-pole — Conductor rated current

**“Wire-to-wire” connection**




Example: female and male connector

**1.5 mm<sup>2</sup> test conductor, fine-stranded**



4-pole — Conductor rated current

**2.5 mm<sup>2</sup> test conductor, fine-stranded**




4-pole — Conductor rated current

# Technical Section

• Current-Carrying Capacity Curve (Derating Curve) to EN 60512-5-2 / Reduction Factor: 0.8


## picoMAX® eCOM, 2091 Series, 3.5 mm pin spacing

“Wire-to-board” connection




Example: 2091-1176 pluggable PCB terminal block

1.0 mm<sup>2</sup> test conductor, fine-stranded



2-, 6-, 12-pole — Conductor rated current


1.5 mm<sup>2</sup> test conductor, fine-stranded



2-, 6-, 12-pole — Conductor rated current


## picoMAX® eCOM, 2092 Series, 5.0 mm pin spacing

“Wire-to-board” connection




Example: 2092-1176 pluggable PCB terminal block

1.5 mm<sup>2</sup> test conductor, fine-stranded



2-, 6-, 12-pole — Conductor rated current

2.5 mm<sup>2</sup> test conductor, fine-stranded



2-, 6-, 12-pole — Conductor rated current


## picoMAX® eCOM, 2092 Series, 7.5 mm pin spacing

“Wire-to-board” connection




Example: 2092-3175 pluggable PCB terminal block

1.5 mm<sup>2</sup> test conductor, fine-stranded



4-pole — Conductor rated current

2.5 mm<sup>2</sup> test conductor, fine-stranded




4-pole — Conductor rated current




- Vibration Test to EN 60068-2-6 for *picoMAX*<sup>®</sup> “Wire-to-Board” Connection

In the vibration test based on EN 60068-2-6, the *picoMAX*<sup>®</sup> “wire-to-board” connection (male header with solder pins and female connector) is tested in a frequency range of 5 to 2,000 Hz with 10 frequency cycles of 17.3 minutes per axis. Acceleration starts with 10 g along all 3 axes and is then gradually increased from 14 g to 16 g, and finally 20 g. A failure occurs when the contact resistance increases by more than 50% of its initial value, or when a contact interruption of more than 20ns is detected.

The test is performed in a cascading manner. This means that every pluggable connector is subjected to all acceleration values up to the maximum acceleration. In this test, the above-mentioned *picoMAX*<sup>®</sup> 2091 Series “wire-to-board” pluggable connection (terminated with 1.5 mm<sup>2</sup>/AWG 14 fine-stranded conductors) achieved an acceleration of 20 g without failure. This value reflects the high vibration-resistance of *picoMAX*<sup>®</sup>. The termination of smaller conductor sizes, as well as both “wire-to-wire” and “board-to-wire” connections, achieve lower acceleration values. The *picoMAX*<sup>®</sup> eCOM pluggable connection, however, is only partly suitable for shock- and vibration-prone environments.



The *picoMAX*<sup>®</sup> female connector is fully shrouded by the male header’s housing, reducing overall connector height. This significantly increases vibration- and shock-resistance via integrated locking latches.




Vibration test performed on a 2091 Series “wire-to-board” connection



## Technical Section

### • Mating Cycle Test

A cascading test sequence is used to determine the mating cycle number of *picoMAX*<sup>®</sup> pluggable connectors. First, a service life test is performed based on IEC/EN 61984, in which the contact surfaces of the pluggable connectors are exposed to mechanical abrasion via mating cycles (i.e., connection and disconnection). Then, an accelerated aging test is performed in industrial atmospheres according to EN ISO 6988. Finally, the pluggable connectors are subjected to a current load cycle test with rated current. A test cycle runs for 30 minutes with current and for 30 minutes without current. Both contact resistance and voltage drop values are determined at the beginning and then continuously monitored during the test. These values have to be within the specified limits. Due to the cascading service life test performed above, up to 25 mating cycles are outlined for practical applications of the *picoMAX*<sup>®</sup> pluggable connection system. More information about connection and disconnection forces are available upon request.



Voltage drop measurement after mating cycle test





Diagram: "Current load cycle with voltage drop progression over 1000 cycles"


According to the cascading service life test, *picoMAX*<sup>®</sup> is suitable for up to 25 mating cycles.

### • Salt Spray Test to IEC/EN 60068-2-11

Ferrules are used to terminate fine-stranded conductors in extremely harsh environmental conditions. Salt spray tests per IEC/EN 60068-2-11 show positive results even after 96 hours in a salt spray chamber.




Salt spray chamber with *picoMAX*<sup>®</sup> test arrangement




*picoMAX*<sup>®</sup> test arrangement after the salt spray test

- Reflow Soldering Processing


picoMAX® male and female headers with solder pins are available in THR variants with 2.4 mm pin projection on the solder side. This pin length is ideal for THR soldering applications with PCB thickness from 1.5 to 2 mm. With the specified solder profile for a four-zone convection reflow oven, both process capability and soldering result for picoMAX® THR versions have been tested for a Sn96.5 Ag3 Cu0.5 lead-free solder.




### Soldering results for picoMAX® – Male headers with solder pins



THR sample board showing picoMAX® male headers with solder pins




Solder joints on the bottom side of the PCB



Drilled hole section


### Soldering results for picoMAX® eCOM – Pluggable PCB connectors



THR sample board showing picoMAX® eCOM



Solder joints on the bottom side of the PCB



Drilled hole section



Item No.	Page	Item No.	Page	Item No.	Page	Item No.	Page
<b>2092 Series</b>							
2092-3302	53						
2092-3303	53						
2092-3304	53						
2092-3305	53						
2092-3322	53						
2092-3323	53						
2092-3324	53						
2092-3325	53						
2092-3352	63						
2092-3353	63						
2092-3354	63						
2092-3355	63						
2092-3372	63						
2092-3373	63						
2092-3374	63						
2092-3375	63						
2092-3402	47						
2092-3402/005-000	48						
2092-3403	47						
2092-3403/005-000	48						
2092-3404	47						
2092-3404/005-000	48						
2092-3405	47						
2092-3405/005-000	48						
2092-3422	47						
2092-3422/005-000	48						
2092-3423	47						
2092-3423/005-000	48						
2092-3424	47						
2092-3424/005-000	48						
2092-3425	47						
2092-3425/005-000	48						
2092-3502/002-000	51						
2092-3504/002-000	51						
2092-3506/002-000	51						
2092-3508/002-000	51						
2092-3522/002-000	51						
2092-3522/020-000	51						
2092-3524/002-000	51						
2092-3524/020-000	51						
2092-3526/002-000	51						
2092-3526/020-000	51						
2092-3528/002-000	51						
2092-3528/020-000	51						
2092-3600	65						
2092-3600/002-000	65						
2092-3601	65						
2092-3601/002-000	65						
2092-3602	65						
2092-3602/002-000	65						
2092-3603	65						
2092-3603/002-000	65						

## Algeria

please contact WAGO France

## Argentina

Bruno Schillig S.A.  
Arenales 4030, B1604CFD  
Florida, PBA  
Phone +54 11 4730 1100  
Fax +54 11 4761 7244  
wago@schillig.com.ar

## Australia

Kontakt Group  
Building Automation & WINSTA Systems  
Office: 730 Springvale Rd  
Mulgrave Victoria 3170  
P.O. Box 3003, Wheelers Hill VIC 3150  
Tel. +61 03 95602757  
Fax +61 03 95601727  
sales@kontaktgroup.com.au

## NHP ELECTRICAL ENGINEERING PRODUCTS PTY LTD

43-67 River Street  
Richmond, Victoria, 3121, P.O. Box 199  
Phone +61 3 9429 2999  
Fax +61 3 9429 1075  
export@wago.com

## Austria

WAGO Kontakttechnik Ges.m.b.H.  
Laxenburger Straße 244  
1230 Wien  
Phone +43 1 6150780  
Fax +43 1 6150775  
info.at@wago.com

## Azerbaijan

AZ Technics LTD  
Zulfi V. Alizade  
Y.Safarov str.33 , AZ1025,  
Baku  
Republic of Azerbaijan  
Tel. +994 12 4968335  
Fax +994 12 4968334  
info@AZtechnics.az

## Belarus

UP FEK  
pr+ Pushkina 29-B  
220015 Minsk  
Phone +375 17 2102189  
Fax +375 17 2102189  
wago@fek.by

## Belgium

WAGO Kontakttechnik  
Excelsiorlaan 11  
1930 Zaventem  
Phone +32 2 7179090  
Fax +32 2 7179099  
info-be@wago.com

## Bosnia and Herzegovina

please contact WAGO Bulgaria

## Brazil

WAGO Eletroeletrônicos Ltda  
Rua Américo Simões 1470  
São Roque da Chave  
Itupeva SP Brasil 13295-000  
Phone +55 11 4591 0199  
Fax +55 11 4591 0190  
info.br@wago.com

## Bulgaria

WAGO Kontakttechnik GmbH & Co. KG  
Business Center Serdika  
2E Akad. Ivan Geshov Blvd.  
Building 1, Floor 4, Office 417  
1330 Sofia  
Phone +359 2 489 46 09  
Fax +359 2 928 28 50  
info-BG@wago.com

## Canada

please contact WAGO USA

## Chile

Desimat Chile  
Av Puerto Vespucio 9670  
Pudahuel Santiago  
Phone +56 2 7470152  
Fax +56 2 7470153  
ventaschile@desimat.cl

## China

WAGO ELECTRONIC (TIANJIN) Co. LTD  
No.5, Quan Hui Road, Wuqing Development Area  
Tianjin 301700  
Phone +86 22 59617688  
Fax +86 22 59617668  
info-cn@wago.com

## Columbia

T.H.L. Ltda.  
Cra. 49 B # 91-33  
Bogotá  
Phone +57 1 621 85 50  
Fax +57 1 621 60 28  
ventas-thl@thl Ltda.com

## Croatia

M.B.A. d.o.o. za trgovinu i zastupanje  
Frana Supila 5  
51211 Matulji HR  
Phone +385 51 275-736  
Fax +385 51 275-066  
mba@ri.htnet.hr

## Croatia

GENERA CTR d.o.o.  
- just for automation technology -  
Siget 18 b  
10020 Zagreb  
Phone +385 13647849  
Fax +385 13636662  
wago@geneza.hr

## Czech Republic

WAGO Elektro spol. sr. o.  
Rozvodova 1116/36  
143 00 Praha 4 - Modřany  
Phone +420 261 090 143  
Fax +420 261 090 144  
info.cz@wago.com

## Denmark

WAGO Danmark  
Filial of WAGO Kontakttechnik GmbH & Co. KG  
Lejrvej 17  
3500 Værløse  
Phone +45 44 357777  
Fax +45 44 357787  
salg.dk@wago.com

## Ecuador

ECUAINSETEC CIA LTDA  
El Zurriago 177 y El Vengador  
Quito  
Phone +593 2 2 26 91 48  
Fax +593 2 2 46 18 33  
g.castro@ecuainsetec.com.ec

## Egypt

IBN Engineering Instrumentation & Control  
71 a El Shaheed Ahmed Hamdi St.  
King Faisal, Giza  
Phone +20 2 7214350  
Fax +20 2 7221709  
sales@ibnengineering.com

## Estonia

Eltarko OÜ  
Laki 14 - 502  
10621 Tallinn  
Phone +372 651 7731  
Fax +372 651 7786  
andres@eltarko.ee

## Finland

WAGO Kontakttechnik GmbH & Co. KG  
Filial i Finland  
Vellamonkatu 30 B  
00550 Helsinki  
Phone +358 9 7744 060  
Fax +358 9 7744 0660  
tilaus@wago.fi

## France

WAGO CONTACT SAS  
Paris Nord 2  
83 Rue des Chardonnerets  
B.P. 55065 - Tremblay en France  
95947 - ROISSY CDG CEDEX  
Phone +33 1 48172590  
Fax +33 1 48632520  
info-fr@wago.com

## Germany

WAGO Kontakttechnik GmbH & Co. KG  
Postfach 28 80, 32385 Minden  
Hansastraße 27  
32423 Minden  
Phone +49 571 887-0  
Fax +49 571 887-169  
info@wago.com

## WAGO Kontakttechnik GmbH & Co. KG

Waldstraße 1  
99706 Sonderhausen  
Phone +49 3632 659-0  
Fax +49 3632 659-100  
info@wago.com

## Great Britain

WAGO limited  
Triton Park, Swift Valley Industrial Estate  
RUGBY  
Warwickshire, CV21 1SG  
Phone +44 1788 568008  
Fax +44 1788 568050  
uksales@wago.com

## Greece

PANAGIOTIS SP. DIMOULAS - BIOMAT  
DIMOULAS AUTOMATIONS  
Kritis Str. 26  
10439 Athen  
Tel. +30 210 883 3337  
Fax +30 210 883 4436  
wago.info@dimoulas.com.gr

## Hong Kong

National Concord Eng., Ltd.  
Unit A-B, 5/F,  
Southeast Industrial Building  
611-619 Castle Peak Road  
Tsuen Wan, N.T.  
Phone +852 24292611  
Fax +852 24292164  
sales@nce.com.hk

## Hungary

WAGO Hungária KFT  
Ipari Park, Gyár u. 2  
2040 Budapest  
Phone +36 23 502-170  
Fax +36 23 502-166  
info.hu@wago.com

## Iceland

S. Gudjonsson ehf.  
Audbrekku 9-11  
202 Kopavogur  
Phone +354 520-4500  
Fax +354 520-4501  
export@wago.com

## India

WAGO & CONTROLS (INDIA) LTD.  
C-27, Sector-38, Phase-III  
Noida-201 301  
Gautam Budh Nagar (U.P.)  
Phone +91 120 2 580409 10  
Fax +91 120 2 580081  
info@wagoindia.com

## Indonesia

please contact WAGO Singapore

## Iraq

please contact WAGO Middle East

## Iran

Patsa Industry  
No. 2 Bahar St.  
South Shiraz Ave  
P.O. Box.: 15875-1698  
14369 Tehran  
Phone +98 21 88047626  
Fax +98 21 88040886  
info.uae@wago.com

## Ireland

Drives & Controls  
Unit F4, Riverview Business Park  
Nangor Road  
Dublin 12  
Phone +353 1 4604474  
Fax +353 1 4604507  
wago@drivesandcontrols.ie

## Israel

Comtel Israel Electronic Solutions Ltd.  
Bet Hapaaon  
20 Hataas Street  
P.O. Box 66  
44425 Kefar-Saba  
Phone +972 9 76 77 240  
Fax +972 9 76 77 243  
sales@comtel.co.il

## Italy

WAGO ELETTRONICA SRL  
Via Parini 1  
40033 Casalecchio di Reno (BO)  
Phone +39 051 6132112  
Fax +39 051 6272174  
info-ita@wago.com

## Japan

WAGO Co. of JAPAN Ltd.  
Nittetsu ND-Tower Building 4F  
Kameido 1-5-7  
Koto-Ku  
Tokyo 136-0071  
Phone +81 3 5627 2050  
Fax +81 3 5627 2055  
info-jp@wago.com

## Kazakhstan

TOO INTANT  
ul. Muratbaeva, d. 61  
050026 Almaty  
Phone +7 727 2371492  
Fax +7 727 2980151  
info@intant.kz

## TOO Technik-Trade

ul. i. A. Protosanova, 81  
070004 Ust-Kamenogorsk  
Phone +7 7232 254064  
Fax +7 7232 253251  
info@technik.kz

## Korea

Mahani Electric Co. Ltd.  
792-7 Yeoksam-Dong  
Kangnam-Gu, 135-080  
Seoul, Korea  
Phone +82 2 2194 3300  
Fax +82 2 2194 3397  
export@wago.com

## Kosovo

please contact WAGO Bulgaria

## Kuwait

Kuwait Controls Company  
Al Sour Street, Above Luffhansa Airline  
Safat Kuwait 13062  
Phone +965 222 54300  
Fax +965 224 33698  
info.uae@wago.com

## Latvia

INSTABALT LATVIA SIA  
Vestienas iela 6  
Riga, LV-1035  
Phone +371 790 1188  
Fax +371 790 1180  
info@instabalt.lv

## Lebanon

Gemayel Trading & Contracting  
Antonios Project  
P.O. BOX 70-1096  
Antelias, Lebanon  
Phone +961 4 521 029  
Fax +961 4 521 029  
gtc.libanon@gmail.com

**Lithuania**

INSTABALT LIU AB  
Savanorių 187  
Vilnius, 2053  
Phone +370 52 322 295  
Fax +370 52 322 247  
info@instabalt.lt

**Luxembourg**

please contact WAGO Belgium

**Macedonia**

please contact WAGO Bulgaria

**Malaysia**

WAGO Representative Office Malaysia  
No 806, Block A4, Leisure Commerce Square,  
No 9, Jalan PJS 8/9, 46150 Petaling Jaya,  
Selangor Darul Ehsan, Malaysia  
Phone +60 3 7877 1776  
Fax +60 3 7877 2776  
kian.guan.tan@wago.com

HPH Materials (M) Sdn Bhd  
No. 4, Jalan Nilam 1/6  
Suban Hi-Tech Industrial Park  
40000 Shah Alam  
Selangor, D.E. Malaysia  
Phone +60 3 5638 2213  
Fax +60 3 5638 8213  
info@hphmaterials.com

Setia Raya Teknik Sdn. Bhd.  
40 & 42 Jalan Nilam SS15/4  
Subang Jaya, 47500 PJ.  
Selangor D.E. Malaysia  
Phone +60 3 5633 5511  
Fax +60 3 5633 3411  
sales@setiaraya.com.my

**Mexico**

WAGO SA de CV  
Av. Del Marques 38 Bodega 3  
P. I. Bernardo Quintana  
76240 El Marques, Querétaro  
Phone +52 442 221 5946  
Fax +52 442 221 5063  
Toll-Free: 001-800-309-5975  
info.mx@wago.com

**Morocco**

please contact WAGO France

**Netherlands**

WAGO Nederland  
Laan van de Ram 19  
7324 BW Apeldoorn  
Phone +31 55 36 83 500  
Fax +31 55 36 83 599  
info-nl@wago.com

**New Zealand**

NHP NZ  
7 Lockhart Place  
Mt Wellington  
New Zealand  
Phone +64 9 2761967  
Fax +64 9 2761992  
export@wago.com

**Norway**

WAGO Norge NUF  
Jerikoveien 20  
1067 Oslo  
Phone +47 22 30 94 50  
Fax +47 22 30 94 51  
info.no@wago.com

**Pakistan**

Fuzilogix Automation & Control  
Suit No. 14, 5th Floor, Shan Arcade  
New Garden Town, Lahore  
Pakistan  
Phone +92 42 594 1503 - 4  
Fax +92 42 585 1431  
info@fuzilogix.com

**Peru**

Desimat Peru  
Av. Velasco Astete 2371  
Surco Lima  
Phone +51 1 2752776  
Fax +51 1 2752765  
export@wago.com

**Philippines**

please contact WAGO Singapore

**Poland**

WAGO ELWAG sp. z o.o.  
ul. Piekna 58 a  
50-506 Wrocław  
Phone +48 71 3602970  
Fax +48 71 3602999  
wago.elwag@wago.com

**Portugal**

MORGADO & CA. LDA - SEDE  
Estrada Exterior da  
Circunvalação 3558/3560  
Apartado 1057  
4435 Rio Tinto  
Phone +351 22 9770600  
Fax +351 22 9770699  
geral@morgadocl.pt

**Republic of Moldova**

Electroservice Slavinschi T.T.  
str. Bolgarskaia 9, office 6  
2001 Kishinev  
Phone +373 22 274427  
Fax +373 22 224481  
es@es.midnet.com

**Romania**

WAGO Kontakttechnik GmbH & Co. KG  
WAGO Representative Office Bucharest  
Str. Nicolae G. Caramfil Nr. 26, Bl. 1D, Et. 3, Ap. 7, Sect. 1, OP52  
014144-Bucuresti, Romania  
Tel. +40-(0)31 421 85 68  
Fax +40-(0)21 232 02 31  
info-RO@wago.com

VDR & Servicii srl  
Str. Valeriu Braniște, nr. 60, ap. 1, sector 3  
Romania  
Phone +40 21 3225074/76  
Fax +40 21 3225075  
office@componente-automatizari.ro

**Russia**

OOO WAGO Kontakt Rus  
Dmitrovskoe shosse, 157, bldg. 12/5  
127411 Moscow  
Russia  
Phone +7 495 9874790  
Fax +7 495 9874791  
info.ru@wago.com

WAGO Branch office  
Ekaterinburg  
Phone +7 343 216 3426

WAGO Branch office  
Novosibirsk  
Phone +7 383 217 9244

WAGO Branch office  
St. Petersburg  
Phone +7 812 312 1918

**Saudi Arabia**

Ali Zaid Al Quraishi & Partners Electrical Services of S.A.  
Al Quraishi Center, King Khalid Street  
P.O. Box 7386  
Dammam - 31462  
Phone +966 3 8351155  
Fax +966 3 8352297  
info.uae@wago.com

**Serbia**

please contact WAGO Bulgaria

Tagor Electronic doo  
Tihomira Brankovica 21  
18000 Nis  
Tel. +381 18 575545  
Fax +381 18 217125  
ana.aleksic@tagor.rs

**Singapore**

WAGO Electronic Pte Ltd  
10 Upper Aljunied Link  
#04-04 Johnson Controls Building  
Singapore 367904  
Phone +65 62866776  
Fax +65 62842425  
info-sing@wago.com

**Slovakia**

WAGO Elektrik spol. s r. o  
Odborárska 52  
83102 Bratislava  
Tel. +421 2 4569 2503  
export@wago.com

**Slovenia**

Proelektro spol. s r.o.  
Na barine 22  
84103 Bratislava Lamač  
Tel. +421 2 4569 2503  
info@wago.sk

**Slovenia**

GENERA d.o.o.  
Prevala 10  
1236 Trzin  
Phone +386 14393050  
Fax +386 14393090  
genera@genera.si

**IC elektronika d.o.o.**

Vodovodna cesta 100  
1000 Ljubljana  
Phone +386 15680110  
Fax +386 15689107  
info@ic-elect.si

**South Africa**

Shorrock Automation (Pty) Ltd  
Postnet Suite # 219  
Private Bag X 8, Elardus Park  
0047 Pretoria  
Phone +27 12 4500300  
Fax +27 12 4500322  
sales@shorrock.co.za

**Spain**

DICOMAT S.L.  
Avda. de la Industria, 36  
Apartado Correos, 1.178  
28108 - Alcobendas (Madrid)  
Phone +34 91 6621362  
Fax +34 91 6610089  
info@dicomat.com

**Sweden**

WAGO Sverige  
WAGO Kontakttechnik GmbH  
Tyskland Filial  
Box 639, 17527 Järfälla  
Datavägen 9 A, 17543 Järfälla  
Phone +46 858410680  
Fax +46 858410699  
info.se@wago.com

**Switzerland**

WAGO CONTACT SA  
Rte. de l'Industrie 19  
Case Postale 168  
1564 Domdidier  
Phone +41/26 676 75 86  
Fax +41/26 676 75 01  
info.switzerland@wago.com

**Syria**

Zahabi Co.  
8/5 Shouhadaa St., P.O. Box 8262  
Aleppo  
Phone +963 21 21 22 235 / 6  
Fax +963 21 21 24 768  
info.uae@wago.com

**Taiwan R.O.C.**

WAGO Contact, Ltd.  
5F., No.168, Jiankang Rd  
Zhonghe City  
Taipei County 23585, Taiwan  
Phone +886 2 22250123  
Fax +886 2 22251511  
info.taiwan@wago.com

**Thailand**

WAGO Representative Office Thailand  
4th Floor, KS Building  
213/6-8 Rachada Phisek Road  
Ding Daeng Bangkok 10320  
Phone +66 2 6935611  
Fax +66 2 6935612  
wago@asianet.co.th

**US Power Distribution Co., Ltd.**

4th Floor K.S. Building  
213/6-8 Rachada Phisek Road  
Ding Daeng, Bangkok 10400  
Phone +66 2 2763040  
Fax +66 2 2763049  
wago@asianet.co.th

**Tunisia**

please contact WAGO France

**Turkey**

WAGO Elektronik Sanayi ve Ticaret Ltd. Şti.  
Yukan Dudullu Mahallesi Bayraktar Bulvan  
Cad. Hattat Sok. No. 10  
34775 Umraniye - Istanbul  
Turkey  
Tel. +90 216 472 1133  
Fax +90 216 472 9910  
info.tr@wago.com

**Ukraine**

NPP Logicon  
Predslavinskaya street, 39, office 303  
03150 Kiev  
Phone +380 44 5228019  
Fax +380 44 2611803  
info@logicon.ua

**OOO Mikropribor**

ul. Kotelnikova, 4  
03115 Kiev  
Phone +380 44 5369386  
Fax +380 44 5369387  
sales@micropribor.kiev.ua

**United Arab Emirates (UAE)**

WAGO Middle East (FZC)  
SAIF Zone, Q4-282  
P.O. Box: 120665  
Sharjah, UAE  
Phone +971 6 5579920  
Fax +971 6 5579921  
info.uae@wago.com

**USA**

WAGO Corporation  
N120 W19129 Freistadt Road  
Germantown, WI 53022  
Phone +1 262 255 6222  
Fax +1 262 255 3232  
Toll-Free: 1-800 DIN Rail (346-7245)  
info.us@wago.com

**Venezuela**


PETROBORNAS, C.A.  
C.C. PLAZA AEROPUERTO - PISO 1 - LOCAL P1 - B - 03  
(8015) UNARE - PUERTO ORDAZ - ESTADO BOLIVAR  
REPÚBLICA BOLIVARIANA DE VENEZUELA  
Tel. +58 286 951 3382  
Fax +58 286 951 3382  
info@petrobomas.com

**Vietnam**

please contact WAGO Germany (Minden)




## Notes






## Notes



## Notes





## WAGO Service Worldwide

### Germany

WAGO Kontakttechnik  
Minden  
Tel. ++49/571/887/0  
Fax ++49/571/887/169

### Austria

WAGO Kontakttechnik  
Wien  
Tel. ++43/1/615/07/80  
Fax ++43/1/615/07/75

### Belgium

WAGO Kontakttechnik  
Zaventem  
Tel. ++32/2/7/17/90/90  
Fax ++32/2/7/17/90/99

### China

WAGO ELECTRONIC Co. Ltd.  
Tianjin  
Tel ++86/22/59617688  
Fax ++86/22/59617668

### England

WAGO, Ltd.  
Rugby  
Tel. ++44/1788/568008  
Fax ++44/1788/568050

### France

WAGO CONTACT S.A.  
Paris  
Tel. ++33/148172590  
Fax ++33/148632520

### Italy

WAGO ELETTRONICA SRL  
Casalecchio di Reno (BO)  
Tel. ++39/051/6132112  
Fax ++39/051/6272174

### Japan

WAGO Co. of JAPAN Ltd.  
Tokyo  
Tel. ++81/3/5627/2050  
Fax ++81/3/5627/2055

### Poland

WAGO ELWAG sp. z o. o.  
Wroclaw  
Tel. ++48/71/3604670/78  
Fax ++48/71/3604699

### Singapore

WAGO Electronic Pte. Ltd.  
Singapore  
Tel. ++65/62866776  
Fax ++65/62842425

### Switzerland

WAGO CONTACT SA  
Domdidier  
Tel. ++41/26/676/75/86  
Fax ++65/26/676/75/01

### Mexico

WAGO Corporation  
Queretaro  
Tel. 001/800/309/5975  
+ 52/442/221/5946  
Fax + 52/442/221/5063

### Canada

WAGO Corporation  
Tel. 800/DIN Rail (346-7245)  
Fax 262/255-3232  
www.wago.ca

WAGO Corporation  
N120 W19129 Freistadt Road  
Germantown, Wisconsin 53022  
Telephone: 800 / DIN Rail (346-7245)  
Fax: 262 / 255-3232  
info.us@wago.com  
www.wago.us  
www.picomax.us

**WAGO**<sup>®</sup>  
INNOVATIVE CONNECTIONS